




Data Sheet	AI-2429-TWT-12V-3-R
------------	---------------------

- Features:**
- Piezo Indicator
 - 12VDC rated, 2900Hz
 - Top-Firing Thru-Hole Type
 - Wave Solder and Wash Allowed


Specifications

Parameters	Values	Units
Rated Voltage	12	VDC
Operating Voltage Range	3 ~ 20	VDC
Current Draw at Rated Voltage	8(Max.)	mA
Minimum SPL @ 10cm	95	dBA
Resonant Frequency	2,900 ± 500	Hz
Tone or Pulse Rate	Continuous	-
Housing Material	ABS777	-
Terminal Material	Sn Plated Copper(DSn)	-
Weight	6	Grams
Acceptable Soldering Methods	Hand Solder, Wave Solder	-
Environmental Compliances	RoHS/REACH	Ex. 7c-1
Storage Temperature	-40 ~ +80	°C
Operating Temperature	-20 ~ +70	°C

Measurement Method (Temperature: 25±3°C; Relative Humidity: 60% ~ 70%)
Standard Test Fixture (Distance: 10cm, 12VDC)



Typical SPL vs Input Voltage




Reliability Testing


Type of Test	Test Specifications
High Temperature Test	Storage in +80°C ± 2°C test box for 96 hours, then expose to the room temperature for 2 hours without applying power.
Low Temperature Test	Storage in -40°C ± 2°C test box for 96 hours, then expose to the room temperature for 2 hours without applying power.
Humidity Test	Storage in +40°C ± 2°C 90-95%RH test box for 96 hours, then expose to the room temperature for 2 hours without applying power.
Temperature Cycle Testing	Make this test for 5 cycles without applying power, then expose to the room temperature for 2 hours.
Vibration Test	Amplitude: 1.5mm Time : 1min/axis Make this test for the directions of X, Y, Z for 2 hours each (total 6 hours)
Solderability Test	Solder Temp 260C for 3 seconds.
Drop Test	Free drop a unit from the height 70cm to the surface of 10mm thick board, three directions (X, Y, Z).
Load Test	If applicable, state the conditions of the load test

Part shall pass tests within SPL of ±5dB.


Recommended Wave Solder Process



Dimensions



Packaging



Specifications Revisions			
Revision	Description	Date	Approved
-	RELEASED FROM ENGINEERING	03/21/2006	-
A	REVISED TONE/PULSE RATE	01/29/2007	RW
B	REVISED TO 3D DRAWING TEMPLATE	01/18/2008	BR
C	REVISED ROHS AND ADDED WAVE SOLDER NOTE	01/25/2019	ML
D	Update Spec Format, Add detail for Reliability, Packaging, etc., Revise Housing Material, Revise Storage Temperature Range	07/08/2024	ML

- Note:
- 1. Unless otherwise specified:
 - A. All dimensions are in millimeters.
 - B. Default tolerances are ±0.5mm and angles are ±3°.
 - 2. Specifications subject to change or withdrawal without notice.
 - 3. Wave solder acceptable.