





PRODUCT NUMBER	PITCH
VIxx21x200J0G	5.08 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:

- Item①Terminal housing :Thermoplastic (UL 94V-0)
- Item②Clamp : Brass ,Ni plated
- Item③Solder pin : Brass , Tin plated
- Item④Terminal screw : Steel Zinc plating"-slot type

Electrical cULus/FIMKO

- Voltage rating: 300VAC/300VAC
- Current rating: 16A/17.5A
- Wire range: 0.5~1.5mm²
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Torque: 3.5Lb-In./0.5Nm
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:

Dimension

DIM A	N×5.08
DIM B	(N-1)×5.08

N=Number of poles

POLES	Tolerance
2p-6p	±0.15
7p-12p	±0.25
13p-16p	±0.35
17p-24p	±0.40

PART NO.: VI xx 2 1 x 2 00J0 G

End stackable	No. of poles	Color	RoHS compliant (lead<4%) In copper Alloy
02	2 poles	0 Black (RAL9005)	
03	3 poles	2 Red (RAL3001/D)	
...	...	3 Orange(RAL2011/P)	
...	...	4 Yellow(RAL1018/A)	
24	24 poles	5 Green(RAL6018/T)	
		6 Blue (RAL5015/A)	
		8 Grey(RAL7035/D)	
		9 White(RAL1102)	
		C Green(RAL6018/U)	

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family
ltr	ecn	no	dr	date	tolerances unless otherwise specified		TERMINAL BLOCK
					angles	MM	title
					0.5		TERMINAL BLOCK
					1		RISING CLAMP,180D WIRE INLET,END STACKABLE
					X.X±0.3		dwg no
					X.XX±0.1		sheet 1 of 1 size
					dr		VIxx21x200J0G
					enr		A4
					chr		type
					appd		CUSTOMER Drawing
sheet index	revision	A	1				