



HONEYWELL PART NUMBER
21EN577-6


REV	DOCUMENT	CHANGED BY	CHECK
A	0012755	KSR 29APR05	AK

B



B

A



- NOTES
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 4
 - 3 - TO ADJUST ROLLER DIRECTION, REMOVE ROLLER GUIDE LOCK RING, SCREW ROLLER GUIDE DOWN AS FAR AS POSSIBLE, THEN UNSCREW TO DESIRED DIRECTION. SECURE BY REPLACING ROLLER GUIDE LOCK RING
 - 4 - CIRCUIT DIAGRAM, CATALOG LISTING, DATE CODE, & FED MFG CODE ARE SHOWN ON NAMEPLATE
 - 5 - REPLACEMENT LOCK RING-PACKET 15PA137
 - 6 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805
 - 7 - WEIGHT: 6.0 OZ MAX

A

A

CHARACTERISTICS	ELECTRICAL DATA		
OPERATING FORCE----- 6-12 LB	CONTACT ARRANGEMENT S P N O		
FULL OVERTRAVEL FORCE----- 30 LB MAX			
RELEASE FORCE----- 4 LB MIN	LOAD	28 VDC	
PRETRAVEL----- .040 MAX		SEA LEVEL	50,000 FT.
DIFFERENTIAL TRAVEL----- .020 MAX	RES	4	4
OVERTRAVEL----- .250 MIN	IND	2	2
	MOTOR	4	
	LAMP		

DESIGN UNITS: INCH			
TOLERANCES UNLESS NOTED:			
NO PLACE	X	±	-
ONE PLACE	.X	±	0.030
TWO PLACE	.XX	±	0.010
THREE PLACE	.XXX	±	0.005
FOUR PLACE	.XXXX	±	-
ANGLES	X	±	-
THIRD ANGLE PROJECTION			

DRAWN	LJB	28MAR05
CHECK	AK	29APR05
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
Pro/ENGINEER	2D	

Honeywell			
TITLE			
SWITCH ENCLOSED			
SIZE	TYPE	DRAWING NAME	REV
B	I	21EN577-6	A
SCALE	1:1	SHEET	1 OF 1