初步数据
Preliminary Data

二极管,逆变器 / Diode, Inverter

最大额定值 / Maximum Rated Values

反向重复峰值电压 Repetitive peak reverse voltage	T_{vj} = 25°C T_{vj} = -25°C	V_{RRM}	3300 3300	V
连续正向直流电流 Continuous DC forward current		I_F	1200	A
正向重复峰值电流 Repetitive peak forward current	t_P = 1 ms	I_{FRM}	2400	A
I2t-值 I²t - value	V_R = 0 V, t_P = 10 ms, T_{vj} = 125°C	I²t	440	kA²s
最大损耗功率 Maximum power dissipation	T_{vj} = 125°C	P_{RQM}	1800	kW
最小开通时间 Minimum turn-on time		$t_{on\ min}$	10,0	µs

特征值 / Characteristic Values

			min.	typ.	max.	
正向电压 Forward voltage	I_F = 1200 A, V_{GE} = 0 V I_F = 1200 A, V_{GE} = 0 V	V_F		2,60 2,55	t.b.d.	V V
反向恢复峰值电流 Peak reverse recovery current	I_F = 1200 A, - di_F/dt = 5400 A/µs (T_{vj}=125°C) V_R = 1800 V V_{GE} = -15 V	I_{RM}		1400 1600		A A
恢复电荷 Recovered charge	I_F = 1200 A, - di_F/dt = 5400 A/µs (T_{vj}=125°C) V_R = 1800 V V_{GE} = -15 V	Q_r		810 1450		µC µC
反向恢复损耗（每脉冲） Reverse recovery energy	I_F = 1200 A, - di_F/dt = 5400 A/µs (T_{vj}=125°C) V_R = 1800 V V_{GE} = -15 V	E_{rec}		750 1500		mJ mJ
结 - 外壳热阻 Thermal resistance, junction to case	每个二极管 / per diode	R_{thJC}			17,0	K/kW
外壳 - 散热器热阻 Thermal resistance, case to heatsink	每个二极管 / per diode λ_{Paste} = 1 W/(m·K) / λ_{grease} = 1 W/(m·K)	R_{thCH}		16,0		K/kW
在开关状态下温度 Temperature under switching conditions		$T_{vj\ op}$	-40		125	°C

prepared by: SB	date of publication: 2013-11-25
approved by: DTS	revision: 2.3

Downloaded from Arrow.com.

初步数据
Preliminary Data


模块 / Module

绝缘测试电压 Isolation test voltage	RMS, f = 50 Hz, t = 1 min.	V_{ISOL}		10,2		kV
局部放电停止电压 Partial discharge extinction voltage	RMS, f = 50 Hz, Q_{PD} typ 10 pC (acc. to IEC 1287)	V_{ISOL}		5,1		kV
DC 稳定性 DC stability	T_{vj} = 25°C, 100 fit	$V_{CE\ D}$		2150		V
模块基板材料 Material of module baseplate				AlSiC		
内部绝缘 Internal isolation	基本绝缘 (class 1, IEC 61140) basic insulation (class 1, IEC 61140)			AlN		
爬电距离 Creepage distance	端子- 散热片 / terminal to heatsink 端子- 端子 / terminal to terminal			64,0 56,0		mm
电气间隙 Clearance	端子- 散热片 / terminal to heatsink 端子- 端子 / terminal to terminal			40,0 26,0		mm
相对电痕指数 Comperative tracking index		CTI		> 600		
			min.	typ.	max.	
外壳 - 散热器热阻 Thermal resistance, case to heatsink	每个模块 / per module λ_{Paste} = 1 W/(m·K) / λ_{grease} = 1 W/(m·K)	R_{thCH}		8,00		K/kW
杂散电感,模块 Stray inductance module		L_{sCE}		25		nH
模块引线电阻,端子-芯片 Module lead resistance, terminals - chip	T_C = 25°C, 每个开关 / per switch	$R_{CC'+EE'}$		0,37		mΩ
储存温度 Storage temperature		T_{stg}	-40		125	°C
模块安装的安装扭距 Mounting torque for modul mounting	螺丝 M6 根据相应的应用手册进行安装 Screw M6 - Mounting according to valid application note	M	4,25	-	5,75	Nm
端子联接扭距 Terminal connection torque	螺丝 M4 根据相应的应用手册进行安装 Screw M4 - Mounting according to valid application note 螺丝 M8 根据相应的应用手册进行安装 Screw M8 - Mounting according to valid application note	M	1,8 8,0	- -	2,1 10	Nm Nm
重量 Weight		G		1000		g


Downloaded from Arrow.com.

初步数据
Preliminary Data


正向偏压特性 二极管,逆变器 (典型)
forward characteristic of Diode, Inverter (typical)
$I_F = f(V_F)$




开关损耗 二极管,逆变器 (典型)
switching losses Diode, Inverter (typical)
$E_{rec} = f(I_F)$
R_{Gon} = Ω, V_{CE} = 1800 V



开关损耗 二极管,逆变器 (典型)
switching losses Diode, Inverter (typical)
$E_{rec} = f(R_G)$
I_F = 1200 A, V_{CE} = 1800 V



瞬态热阻抗 二极管,逆变器
transient thermal impedance Diode, Inverter
$Z_{thJC} = f(t)$




prepared by: SB	date of publication: 2013-11-25
approved by: DTS	revision: 2.3

Downloaded from Arrow.com.

初步数据
Preliminary Data

安全工作区 二极管,逆变器 (SOA)
safe operation area Diode, Inverter (SOA)
$I_R = f(V_R)$
$T_{vj} = 125°C$




prepared by: SB	date of publication: 2013-11-25
approved by: DTS	revision: 2.3


Downloaded from Arrow.com.

初步数据
Preliminary Data

接线图 / circuit_diagram_headline



封装尺寸 / package outlines



prepared by: SB	date of publication: 2013-11-25
approved by: DTS	revision: 2.3

Downloaded from Arrow.com.

初步数据
Preliminary Data

使用条件和条款

使用条件和条款
产品规格书中的数据是专门为技术人员提供的，您和您的技术部门应该针对您的应用来评估产品及产品的所有参数是否适合

产品规格书中所描述的产品特性是被保证的，任何这种保证严格依照供货协议中所涉及的条件和条款。除此之外，产品和产品的特性没有任何的保证
请注意安装及应用指南中的信息。

如果您有超出规格书所提供的产品信息的要求或者对我们的产品针对的特殊应用有疑虑的话，请联系我们负责你的销售部门（详情查询 www.infineon.com ）。对那些特别感兴趣的问题我们将提供相应的应用手册
由于技术需要，我们的产品可能含有危险物质。如果需要查询类似问题请联系我们负责你的销售部门
如果您想将我们的产品用于航天，健康，危及生命或者生命维持等应用，请申明。
请注意，对这类应用我们强烈建议
-执行联合的风险和质量评估
-得到质量协议的结论
- 建立联合的测试和出厂产品检查， 我们可以根据测试的实际情况供货
如果有必要，请根据实际需要将类似的说明给你的客户
保留产品规格书的修改权

Terms & Conditions of usage

The data contained in this product data sheet is exclusively intended for technically trained staff. You and your technical departments will have to evaluate the suitability of the product for the intended application and the completeness of the product data with respect to such application.

This product data sheet is describing the characteristics of this product for which a warranty is granted. Any such warranty is granted exclusively pursuant the terms and conditions of the supply agreement. There will be no guarantee of any kind for the product and its characteristics. The information in the valid application- and assembly notes of the module must be considered.

Should you require product information in excess of the data given in this product data sheet or which concerns the specific application of our product, please contact the sales office, which is responsible for you (see www.infineon.com). For those that are specifically interested we may provide application notes.

Due to technical requirements our product may contain dangerous substances. For information on the types in question please contact the sales office, which is responsible for you.

Should you intend to use the Product in aviation applications, in health or live endangering or life support applications, please notify. Please note, that for any such applications we urgently recommend
- to perform joint Risk and Quality Assessments;
- the conclusion of Quality Agreements;
- to establish joint measures of an ongoing product survey, and that we may make delivery depended on the realization of any such measures.

If and to the extent necessary, please forward equivalent notices to your customers.

Changes of this product data sheet are reserved.

prepared by: SB	date of publication: 2013-11-25
approved by: DTS	revision: 2.3

Downloaded from Arrow.com.