


LTE IoT 11 Click



PID: MIKROE-5863

LTE IoT 11 Click is a compact add-on board with an optimized global coverage module, as it supports a comprehensive set of bands required for global deployment. This board features the [TX62-W](#), a global MTC module from [Telit Cinterion](#). It delivers global LTE-M, NB-IoT (NB1 and NB2) connectivity from a single SKU, and it is the first Telit Cinterion product to adopt a revolutionary “Things” footprint. Besides, it integrates an embedded GNSS multi-constellation, state-of-the-art secure services, and more. This Click board™ makes the perfect solution for the development of mission-critical IoT applications, logistics and asset tracking, predictive maintenance, industrial, smart agriculture, and many more.

LTE IoT 11 Click is supported by a [mikroSDK](#) compliant library, which includes functions that simplify software development. This [Click board™](#) comes as a fully tested product, ready to be used on a system equipped with the [mikroBUS™](#) socket.

How does it work?

LTE IoT 11 Click is based on the TX62-W, a global MTC module from Telit Cinterion. It is a highly efficient module and delivers global LPWAN LTE connectivity leveraging mature Rel. 14 second-generation Cat. M1/NB1/NB2 with speeds up to 1.1Mbps. The TX61-W supports optimized 3GPP power modes PSM, an eDRx revolutionizing possibilities for battery-operated cellular devices. All this, combined with integrated GNSS support (GPS/GALILEO/GLONASS/BeiDou), provides a steady stream of limiting and location information for precision positioning data anywhere in the world. This ultra-integrated IoT module comes with a unique architecture that allows the flexibility to run applications with a host MCU or inside the module itself. In addition, the module supports Cinterion IoT Suite Services as an optional platform that manages the connectivity.

Mikroe produces entire development toolchains for all major microcontroller architectures.


Committed to excellency, we are dedicated to helping engineers bring the project development up to speed and achieve outstanding results.



ISO 27001: 2013 certification of informational security management system.
ISO 14001: 2015 certification of environmental management system.
OHSAS 18001: 2008 certification of occupational health and safety management system.



ISO 9001: 2015 certification of quality management system (QMS).



The TX62-W module supports embedded Ipv4 and Ipv6 TCP/IP stack access and transparent TCP/UDP services. Internet services TCP server/client, UDP client, DNS, Ping, HTTP client, FTP client, and MQTT client are also supported. As for security, the module supports secure connection with TLS/DTLS and secure boot.

LTE IoT 11 Click is equipped with two SMA connectors for connecting appropriate antennas that MIKROE offers, and you shouldn't use this Click board™ without them. There are two LEDs, RX/TX, and STAT, for status indication. The microSIM card holder is placed at the bottom side of the board. The TX62-W also supports an eUICC interface in MFF-XS format. The interface is available as an 8-pin pad header. The VPP SEL jumper at the bottom is used for a single-wire protocol and is part of the eUICC interface. If you plan to use an external SWP master, you should connect this jumper to a VCC.

LTE IoT 11 Click can communicate with the host MCU using several interfaces. The default interface is selected over the COMM SEL jumpers as a UART serial interface with commonly used UART RX and TX lines. Using the UART interface, you can also count on the hardware control flow UART RTS and CTS pins. MIKROE offers the appropriate library for this Click board™, but you can also use the AT command set to control the module. You can change it to the SPI serial interface if it better suits you and count to transmission rates of up to 6.5Mbps. In addition, you can use the I2C interface supporting up to 400kbps in Fast Mode for the same purpose.

The LTE IoT 11 Click uses the SMI pin as a suspend mode indicator, indicating the host MCU when the module enters the Suspend mode. This feature can be turned ON/OFF by the software. The ON pin or the ON onboard button can do the fast shutdown. The TX62-W also supports a direct USB 2.0 connection, with a 480Mbps high-speed, that can be used over the 3-pin header. The USB interface is intended for use as a trace interface only. However, you can access the UART interface of the TX62-W modem over the USB C connector and the [FT230x](#), a USB to basic UART IC from FTDI.

As the TX62-W works on lower voltages, the LTE IoT 11 Click features the [TXB0106](#), a 6-bit bidirectional level-shifting and voltage translator from Texas Instruments. In addition, it uses for the same purpose the [NVT2010](#), a bidirectional voltage-level translator from NXP. There are the [TPS7A7002](#) and the LP2985 for additional voltage regulations, both LDOs from Texas Instruments. There is a VCORE as a recommended testing pad, where you can check the voltages of the core during normal operation, sleep mode operation, and suspend mode operation.

Mikroe produces entire development toolchains for all major microcontroller architectures.

Committed to excellency, we are dedicated to helping engineers bring the project development up to speed and achieve outstanding results.



ISO 27001: 2013 certification of informational security management system.
ISO 14001: 2015 certification of environmental management system.
OHSAS 18001: 2008 certification of occupational health and safety management system.



ISO 9001: 2015 certification of quality management system (QMS).

This Click board™ can operate with either 3.3V or 5V logic voltage levels selected via the VCC SEL jumper. This way, both 3.3V and 5V capable MCUs can use the communication lines properly. Also, this Click board™ comes equipped with a library containing easy-to-use functions and an example code that can be used as a reference for further development.

Specifications

Type	GPS/GNSS,LTE IoT
Applications	Can be used for the development of mission-critical IoT applications, logistics and asset tracking, predictive maintenance, industrial, smart agriculture, and many more
On-board modules	TX62-W - global MTC module from Telit Cinterion
Key Features	An ultra-integrated module featuring embedded GNSS multi-constellation (GPS, Galileo, Glonass, BeiDou), state-of-the-art secure services, 3GPP Rel.14 compliant protocol (LET Cat M1/NB1/NB2, SMA antennas, microSIM card socket, eUICC support, AT commands support, USB C connector for UART serial connection to the PC, SUB 2.0 support, and more
Interface	I2C,SPI,UART,USB
Feature	No ClickID
Compatibility	mikroBUS™
Click board size	L (57.15 x 25.4 mm)
Input Voltage	3.3V or 5V

Pinout diagram

This table shows how the pinout on LTE IoT 11 Click corresponds to the pinout on the mikroBUS™ socket (the latter shown in the two middle columns).

Notes	Pin					Pin	Notes
Suspend Mode Indicator	SMI	1	AN	PWM	16	CTS	UART CTS
Module ON	ON	2	RST	INT	15	RTS	UART RTS
SPI Chip Select	CS	3	CS	RX	14	TX	UART TX
SPI Clock	SCK	4	SCK	TX	13	RX	UART RX
SPI Data OUT	SDO	5	MISO	SCL	12	SCL	I2C Clock
SPI Data IN	SDI	6	MOSI	SDA	11	SDA	I2C Data
Power Supply	3.3V	7	3.3V	5V	10	5V	Power Supply
Ground	GND	8	GND	GND	9	GND	Ground

Onboard settings and indicators

Label	Name	Default	Description
Mikroe produces entire development toolchains for all major microcontroller architectures. Committed to excellency, we are dedicated to helping engineers bring the project development up to speed and achieve outstanding results.   ISO 27001: 2013 certification of informational security management system. ISO 14001: 2015 certification of environmental management system. OHSAS 18001: 2008 certification of occupational health and safety management system.  ISO 9001: 2015 certification of quality management system (QMS).			

LD1	PWR	-	Power LED Indicator
LD2	RX/TX	-	RX/TX LED Indicator
LD5	STAT	-	Status LED Indicator
JP1-JP5	COMM SEL	Left	Communication Interface Selection UART/SPI: Left position UART, Right position SPI
JP3	VCC SEL	Left	Power/Logic Voltage Level Selection 3V3/5V: Left position 3V3, Right position 5V
JP6	VPP SEL	Lower	Single Wire Protocol Selection VCC1V8/GND: Up position VCC1V8, Down position GND
T1	ON	-	Module ON Button

LTE IoT 11 Click electrical specifications

Description	Min	Typ	Max	Unit
Supply Voltage	3.3	-	5	V
GNSS Operating Frequency	1573.397	-	1606.563	MHz
LTE Operating Frequency	450	-	2.100	MHz
Data Rate	-	-	1.1	Mbps
Horizontal Accuracy	-	3	-	m

Software Support

We provide a library for the LTE IoT 11 Click as well as a demo application (example), developed using MIKROE [compilers](#). The demo can run on all the main MIKROE [development boards](#).

Package can be downloaded/installed directly from NECTO Studio Package Manager (recommended), downloaded from our [LibStock™](#) or found on [Mikroe github account](#).

Library Description

This library contains API for LTE IoT 11 Click driver.

Key functions

- lteiot11_set_sim_apn This function sets APN for sim card.
- lteiot11_send_sms_text This function sends text message to a phone number.
- lteiot11_parse_gga This function parses the GGA data from the read response buffer.

Example Description

Mikroe produces entire development toolchains for all major microcontroller architectures.
Committed to excellency, we are dedicated to helping engineers bring the project development up to speed and achieve outstanding results.



ISO 27001: 2013 certification of informational security management system.
ISO 14001: 2015 certification of environmental management system.
OHSAS 18001: 2008 certification of occupational health and safety management system.



ISO 9001: 2015 certification of quality management system (QMS).

Application example shows device capability of connecting to the network and sending SMS or TCP/UDP messages, or retrieving data from GNSS using standard "AT" commands.

The full application code, and ready to use projects can be installed directly from NECTO Studio Package Manager (recommended), downloaded from our [LibStock™](#) or found on [Mikroe github account](#).

Other Mikroe Libraries used in the example:

- MikroSDK.Board
- MikroSDK.Log
- Click.LTEIoT11

Additional notes and informations

Depending on the development board you are using, you may need [USB UART click](#), [USB UART 2 Click](#) or [RS232 Click](#) to connect to your PC, for development systems with no UART to USB interface available on the board. UART terminal is available in all MIKROE [compilers](#).

mikroSDK

This Click board™ is supported with [mikroSDK](#) - MIKROE Software Development Kit. To ensure proper operation of mikroSDK compliant Click board™ demo applications, mikroSDK should be downloaded from the [LibStock](#) and installed for the compiler you are using.

For more information about mikroSDK, visit the [official page](#).

Resources

[mikroBUS™](#)

[mikroSDK](#)

[Click board™ Catalog](#)

[Click boards™](#)

Downloads

[TXB0106 datasheet](#)

[FT230X datasheet](#)

[TPS7A7002 datasheet](#)

[NVT2010 datasheet](#)

[LTE IoT 11 click example on Libstock](#)

[LTE IoT 11 click schematic](#)

[AT commands](#)

[LTE IoT 11 click 2D and 3D files](#)

Mikroe produces entire development toolchains for all major microcontroller architectures.

Committed to excellency, we are dedicated to helping engineers bring the project development up to speed and achieve outstanding results.



ISO 27001: 2013 certification of informational security management system.
ISO 14001: 2015 certification of environmental management system.
OHSAS 18001: 2008 certification of occupational health and safety management system.



ISO 9001: 2015 certification of quality management system (QMS).



Time-saving embedded tools

MIKROELEKTRONIKA D.O.O, Barajnički drum 23, 11000 Belgrade, Serbia

VAT: SR105917343 Registration No. 20490918

Phone: + 381 11 78 57 600 Fax: + 381 11 63 09 644 E-mail: office@mikroe.com

www.mikroe.com

Mikroe produces entire development toolchains for all major microcontroller architectures.

Committed to excellency, we are dedicated to helping engineers bring the project development up to speed and achieve outstanding results.



ISO 27001: 2013 certification of informational security management system.
ISO 14001: 2015 certification of environmental management system.
OHSAS 18001: 2008 certification of occupational health and safety management system.



ISO 9001: 2015 certification of quality management system (QMS).