


# Phase Control Thyristors

$$V_{RRM} = 800-1600 \text{ V}$$


$$I_{T(RMS)} = 50 \text{ A}$$

$$I_{T(AV)M} = 32 \text{ A}$$

| $V_{RSM}$<br>$V_{DSM}$<br>V | $V_{RRM}$<br>$V_{DRM}$<br>V | Type        |
|-----------------------------|-----------------------------|-------------|
| 900                         | 800                         | CS 23-08io2 |
| 1300                        | 1200                        | CS 23-12io2 |
| 1700                        | 1600                        | CS 23-16io2 |



TO-208AA  
(TO-48)



1 = Anode, 2 = Cathode, 3 = Gate

| Symbol         | Test Conditions                                                                                                                                           | Maximum Ratings                                                                                                                    |
|----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| $I_{T(RMS)}$   | $T_{VJ} = T_{VJM}$                                                                                                                                        | 50 A                                                                                                                               |
| $I_{T(AV)M}$   | $T_{case} = 85^{\circ}\text{C}; 180^{\circ}$ sine                                                                                                         | 25 A                                                                                                                               |
|                | $T_{case} = 69^{\circ}\text{C}; 180^{\circ}$ sine                                                                                                         | 32 A                                                                                                                               |
| $I_{TSM}$      | $T_{VJ} = 45^{\circ}\text{C};$<br>$V_R = 0$                                                                                                               | $t = 10 \text{ ms}$ (50 Hz), sine<br>450 A<br>$t = 8.3 \text{ ms}$ (60 Hz), sine<br>480 A                                          |
|                | $T_{VJ} = T_{VJM}$<br>$V_R = 0$                                                                                                                           | $t = 10 \text{ ms}$ (50 Hz), sine<br>400 A<br>$t = 8.3 \text{ ms}$ (60 Hz), sine<br>430 A                                          |
| $I^2t$         | $T_{VJ} = 45^{\circ}\text{C}$<br>$V_R = 0$                                                                                                                | $t = 10 \text{ ms}$ (50 Hz), sine<br>1010 $\text{A}^2\text{s}$<br>$t = 8.3 \text{ ms}$ (60 Hz), sine<br>970 $\text{A}^2\text{s}$   |
|                | $T_{VJ} = T_{VJM}$<br>$V_R = 0$                                                                                                                           | $t = 10 \text{ ms}$ (50 Hz), sine<br>800 $\text{A}^2\text{s}$<br>$t = 8.3 \text{ ms}$ (60 Hz), sine<br>770 $\text{A}^2\text{s}$    |
| $(di/dt)_{cr}$ | $T_{VJ} = T_{VJM}$<br>$f = 50 \text{ Hz}, t_p = 200 \mu\text{s}$<br>$V_D = 2/3 V_{DRM}$<br>$I_G = 0.3 \text{ A}$<br>$di_G/dt = 0.3 \text{ A}/\mu\text{s}$ | repetitive, $I_T = 75 \text{ A}$<br>150 $\text{A}/\mu\text{s}$<br>non repetitive, $I_T = I_{T(AV)M}$<br>500 $\text{A}/\mu\text{s}$ |
| $(dv/dt)_{cr}$ | $T_{VJ} = T_{VJM};$<br>$R_{GK} = \infty;$ method 1 (linear voltage rise)                                                                                  | $V_{DR} = 2/3 V_{DRM}$<br>1000 $\text{V}/\mu\text{s}$                                                                              |
| $P_{GM}$       | $T_{VJ} = T_{VJM}$<br>$I_T = I_{T(AV)M}$                                                                                                                  | $t_p = 30 \mu\text{s}$<br>10 W<br>$t_p = 300 \mu\text{s}$<br>5 W                                                                   |
| $P_{G(AV)}$    |                                                                                                                                                           | 0.5 W                                                                                                                              |
| $V_{RGM}$      |                                                                                                                                                           | 10 V                                                                                                                               |
| $T_{VJ}$       |                                                                                                                                                           | -40...+125 $^{\circ}\text{C}$                                                                                                      |
| $T_{VJM}$      |                                                                                                                                                           | 125 $^{\circ}\text{C}$                                                                                                             |
| $T_{stg}$      |                                                                                                                                                           | -40...+125 $^{\circ}\text{C}$                                                                                                      |
| $M_d$          | Mounting torque                                                                                                                                           | 2.7-3.3 Nm<br>24-29 lb.in.                                                                                                         |
| Weight         |                                                                                                                                                           | 12 g                                                                                                                               |

## Features

- Thyristor for line frequencies
- International standard package JEDEC TO-208AA
- Planar glassivated chip
- Long-term stability of blocking currents and voltages


## Applications

- Motor control
- Power converter
- AC power controller

## Advantages

- Space and weight savings
- Simple mounting
- Improved temperature and power cycling

## Dimensions in mm (1 mm = 0.0394")



Data according to IEC 60747

IXYS reserves the right to change limits, test conditions and dimensions

| Symbol     | Test Conditions                                                                                                                                                  | Characteristic Values  |
|------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------|
| $I_R, I_D$ | $T_{VJ} = T_{VJM}; V_R = V_{RRM}; V_D = V_{DRM}$                                                                                                                 | $\leq 3$ mA            |
| $V_T$      | $I_T = 80$ A; $T_{VJ} = 25^\circ\text{C}$                                                                                                                        | $\leq 1.8$ V           |
| $V_{T0}$   | For power-loss calculations only ( $T_{VJ} = 125^\circ\text{C}$ )                                                                                                | 1.0 V                  |
| $r_T$      |                                                                                                                                                                  | 10 m $\Omega$          |
| $V_{GT}$   | $V_D = 6$ V; $T_{VJ} = 25^\circ\text{C}$                                                                                                                         | $\leq 2.5$ V           |
|            | $T_{VJ} = -40^\circ\text{C}$                                                                                                                                     | $\leq 3.5$ V           |
| $I_{GT}$   | $V_D = 6$ V; $T_{VJ} = 25^\circ\text{C}$                                                                                                                         | $\leq 50$ mA           |
|            | $T_{VJ} = -40^\circ\text{C}$                                                                                                                                     | $\leq 80$ mA           |
| $V_{GD}$   | $T_{VJ} = T_{VJM}; V_D = 2/3 V_{DRM}$                                                                                                                            | $\leq 0.2$ V           |
| $I_{GD}$   |                                                                                                                                                                  | $\leq 1$ mA            |
| $I_L$      | $T_{VJ} = 25^\circ\text{C}; t_p = 10$ $\mu\text{s}$<br>$I_G = 0.15$ A; $di_G/dt = 0.15$ A/ $\mu\text{s}$                                                         | $\leq 200$ mA          |
| $I_H$      | $T_{VJ} = 25^\circ\text{C}; V_D = 6$ V; $R_{GK} = \infty$                                                                                                        | $\leq 100$ mA          |
| $t_{gd}$   | $T_{VJ} = 25^\circ\text{C}; V_D = 1/2 V_{DRM}$<br>$I_G = 0.15$ A; $di_G/dt = 0.15$ A/ $\mu\text{s}$                                                              | $\leq 2$ $\mu\text{s}$ |
| $t_q$      | $T_{VJ} = T_{VJM}; I_T = 25$ A, $t_p = 300$ $\mu\text{s}$ ; $di/dt = -20$ A/ $\mu\text{s}$<br>$V_R = 100$ V; $dv/dt = 20$ V/ $\mu\text{s}$ ; $V_D = 2/3 V_{DRM}$ | typ. 60 $\mu\text{s}$  |
| $R_{thJC}$ | DC current                                                                                                                                                       | 1.0 K/W                |
| $R_{thJH}$ | DC current                                                                                                                                                       | 1.61 K/W               |
| $d_s$      | Creepage distance on surface                                                                                                                                     | 1.5 mm                 |
| $d_A$      | Strike distance through air                                                                                                                                      | 1.5 mm                 |
| $a$        | Max. acceleration, 50 Hz                                                                                                                                         | 50 m/s <sup>2</sup>    |

Accessories:

Nut M6 DIN 439/SW14

Lock washer A6 DIN 128




Fig. 1 Gate voltage and gate current  
Triggering:  
A = no; B = possible; C = safe




Fig. 2 Gate controlled delay time  $t_{gd}$




Fig. 3 On-state characteristics




Fig. 4 Surge overload current  
 $I_{TSM}$ : crest value,  $t$ : duration




Fig. 5  $I^2t$  versus time (1-10 ms)




Fig. 6 Maximum forward current at case temperature 180° sine




Fig. 7 Power dissipation versus on-state current and ambient temperature




Fig. 8 Transient thermal impedance junction to heatsink

$R_{thJH}$  for various conduction angles  $d$ :

| $d$  | $R_{thJH}$ (K/W) |
|------|------------------|
| DC   | 1.61             |
| 180° | 1.85             |
| 120° | 2.03             |
| 60°  | 2.35             |
| 30°  | 2.60             |

Constants for  $Z_{thJH}$  calculation:

| $i$ | $R_{thi}$ (K/W) | $t_i$ (s) |
|-----|-----------------|-----------|
| 1   | 0.224           | 0.003     |
| 2   | 0.132           | 0.028     |
| 3   | 0.321           | 0.216     |
| 4   | 0.522           | 1.1       |
| 5   | 0.249           | 4.2       |
| 6   | 0.162           | 43.2      |