





PART NO.	ENG. NO.	TERM PATTERN		
		1	2	3
09-18-5032	A-1840-3-01	M	M	M
09-18-5031	A-1840-3-02	F	M	M
09-18-5037	A-1840-3-07	M	F	M
09-18-5930	A-1840-3-09	M	B	M



SECTION "A-A"



SCALE: 4:1

A-1840-3-2 SHOWN

NOTES:

1. MATERIAL:

BASE AND RECEPTACLE: NYLON PA66, UL94V-0, COLOR: NATURAL
TERMINALS: MALE - BRASS ALLOY
FEMALE - PHOSPHOR BRONZE ALLOY

2. FINISH:

MALE TERMINALS: .000200/0.00508 MIN. TIN OVER
.000100/0.00254 MIN. COPPER
FEMALE TERMINALS: .000050/0.00127 MIN. TIN OVER
.000050/0.00127 MIN. NICKEL

3. PRODUCT SPECIFICATION: N/A

4. PACKAGING SPECIFICATION: PK-1840-001

5. POLARIZATION ACCOMPLISHED THROUGH AN INTER-MIX OF MALE AND FEMALE TERMINALS. (MOLEX .093 TERMINALS)

6. TERMINAL PATTERN CODE:

M = MALE TERMINALS
F = FEMALE TERMINALS
B = NO TERMINALS

7. PARTS TO BE MOUNTED ON SUPPORTED EDGE OF P.C. BOARD

ADD PKG SPECS EC NO: UCP2013-4695 DRAWN:MMSTROH 2011/10/18 CHKD:JBELL 2013/05/01 APPR:FSM/TH 2013/05/13 V2	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION					
					IN/MM		6:1	INCH						
			4 PLACES	± ---	± ---	DRAWN BY	DATE	CONNECTOR-P.C. BOARD WAFERCONN 3 CIRCUIT						
			3 PLACES	± ---	± .010	CHECKED BY	DATE							
			2 PLACES	± 0.25	± .015	JBELL	2013/05/01							
			1 PLACE	± 0.38	± ---	APPROVED BY	DATE							
			ANGULAR ±1/2°					molex		MOLEX INCORPORATED				
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.						DOCUMENT NO.		SHEET NO.
						SEE CHART						SDA-1840-3-*		1 OF 1
						SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							