

ACRK-22-01-G-T-B1-P-1

ACRK-22-05-G-T-B1-M-1

ACRK-22 SERIES

22 mm IP68 FIELD TERMINATION KIT

SPECIFICATIONS

For complete specifications and processing guidelines see www.samtec.com?ACRK-22

Terminal Material:

Brass

Contact Material:

Brass/BeCu

Operating Temp Range:

-10 °C to +105 °C

Housing:

-P: Thermoplastic

-M: Zinc Alloy

RoHS Compliant:

Yes

Mates with:


ACP-22, ACPK-22

CURRENT RATING		
LEAD STYLE	PINS POWERED	CCC per PIN
-01	30	2.0 A
-02	20	2.3 A
-03	8	8.3 A

For general reference only. See www.samtec.com?ACRK-22 for complete test data or contact AcciMate@samtec.com for applications requiring higher current carrying capacity.


DUST CAPS

- DCA-ACR-22-M-X (Metal)
- DCA-ACR-22-P-X (Plastic)



- Visit sealedio.samtec.com for a complete list of sealed systems


PANEL OPENING



NOTE

For complete specifications and processing guidelines see www.samtec.com?ACRK-22

Note:
Some lengths, styles and options are non-standard, non-returnable.



ACRK - 22 - LEAD STYLE - PLATING - GENDER - TERMINATION - HOUSING MATERIAL - KEY

-01
= 1.0 mm DIA (30)
(20-24 AWG)

-02
= 1.0 mm DIA (20)
(20-24 AWG)

-03
= 1.5 mm DIA (8)
(14-18 AWG)


-G
= 10 μ" (0.25 μm)
Gold over 50 μ" (1.27 μm)
Ni on contact

-T
= Terminal
-S
= Socket


-C
= Solder Cup
-B1
= (1.60 mm) .062" Board Mount

-P
= Plastic
-M
= Metal


-1
= Orange, 45°




-01



-02



-03



-C END SHOWN