



## 2-6605814-5 Product Details

Share Print Email



2-6605814-5

TE Internal Number: 2-6605814-5

Active

View 3D PDF

### Mag45 - RJ45 with Integrated Magnetics

Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- Connector
- Gigabit Ethernet Application
- Number of Cores = 12
- Operating Temperature = 0 - 70 °C
- Status Indicator = LED

[View all Features](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [1X1 MAG45\(TM\), MODULAR JACK, 7G4 SCHEMATIC, 05 SERIE...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: (CAD Format & Compression Information)

- [2D Drawing](#) (DXF, Version H)
- [3D Model](#) (IGES, Version H)
- [3D Model](#) (STEP, Version H)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Connector
- Number of Cores = 12
- Magnetics = Integrated Magnetics
- Jack Type = RJ45
- Signal Routing Type = Auto MDI/MDIX
- Profile = Standard
- PCB Mounting Orientation = Side Entry (Right Angle)

#### Mechanical Attachment:

- [Jack Configuration](#) = 1 x 1

#### Electrical Characteristics:

- [Turns Ratio](#) = 1:1
- Shielded = Yes

#### Termination Features:

- [EMI Finger - Bottom](#) = Without
- [Termination Method](#) = Solder

#### Body Features:

- Port Configuration = Single
- EMI Fingers -Top and Sides = With
- Latch Orientation = Inverted - Latch Up
- PCB Tail Length (mm [in]) = 2.54 [0.100]

#### Contact Features:

- Contact Termination Type = Through Hole
- Preloaded = Yes

#### Housing Features:

- Connector Style = Jack

#### Configuration Features:

- Status Indicator = LED
- Decoupling Capacitor = 2KV
- [Rear PCB Ground Tab](#) = Without
- Signal Lead Quantity = 10

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Identification Marking:

- Left LED Color (Position #1) = Green/Yellow (Bicolor)
- Right LED Color (Position #2) = Green

#### Environmental:

- Operating Temperature (°C [°F]) = 0 - 70 [32 - 158]

#### Conditions for Usage:

- Applies To = Printed Circuit Board
- Environmental Conditions = Office / Premises

#### Operation/Application:

- [Application](#) = Gigabit Ethernet

#### Other:

- PlanarMag = No
- Brand = Tyco Electronics

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

