



Color: ■ gray

Physical data

Width	1.5 mm / 0.059 inches
Height	99.3 mm / 3.909 inches
Depth	50.5 mm / 1.988 inches

Mechanical data

Use	with lock-out seal option
Mounting type	snap-on type

Material data

Note (material data)	Information on material specifications can be found here
Color	gray
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.153 MJ
Weight	5.7 g

Environmental requirements

Environmental Testing		Environmental Testing	
Test specification: Railway applications – Rolling stock – Electronic equipment	DIN EN 50155 (VDE 0115-200):2022-06	Acceleration	0.101g (highest test level used for all axes)
Test procedure: Railway applications – Rolling stock equipment – Vibration and shock tests	DIN EN 61373 (VDE 0115-0106):2011-04	Test duration per axis	10 min.
Spectrum/Mounting location	Service life test, Category 1, Class A/B	Test directions	X, Y and Z axes
Functional test with noise-like oscillations	Test passed according to Section 8 of the standard	Monitoring of contact faults and interruptions	Passed
Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$	Voltage drop measurement before and after each axis	Passed
		Simulated service life test through increased levels of noise-like oscillations	Test passed according to Section 9 of the standard
		Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$

Environmental Testing

Acceleration	0.572g (highest test level used for all axes)
Test duration per axis	5 h
Test directions	X, Y and Z axes
Extended testing: Monitoring of contact faults and interruptions	Passed
Extended testing: Voltage drop measurement before and after each axis	Passed
Shock test	Test passed according to Section 10 of the standard
Shock pulse form	Half sine
Acceleration	5g (highest test level used for all axes)
Shock duration	30 ms
Number of shocks (per axis)	3 pos. und 3 neg.
Test directions	X, Y and Z axes
Extended testing: Monitoring of contact faults and interruptions	Passed
Extended testing: Voltage drop measurement before and after each axis	Passed
Vibration and shock stress for rolling stock equipment	Passed

Commercial data

Product Group	22 (TOPJOB S)
PU (SPU)	50 (10) pcs
Packaging type	Box
Country of origin	DE
GTIN	4050821458401
Customs tariff number	85389099990

Product Classification

UNSPSC	39121702
eCl@ss 10.0	27-14-11-33
eCl@ss 9.0	27-14-11-33
ETIM 9.0	EC000886
ETIM 10.0	EC000886
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Approvals / Certificates

Declarations of conformity and manufacturer's declarations



Approval	Standard	Certificate Name
Railway WAGO GmbH & Co. KG	-	Railway Ready

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 2007-8893



Documentation

Bid Text

2007-8893	19.02.2019	xml 2.57 KB	
2007-8893	28.04.2017	doc 23.00 KB	

CAD/CAE-Data

CAD data

2D/3D Models
2007-8893



CAE data

EPLAN Data Portal
2007-8893



WSCAD Universe
2007-8893



ZUKEN Portal
2007-8893



Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com