




TE Internal #: 62827-1

Quick Disconnect Tab, Uninsulated, 23 – 22 AWG, .26 – .33 mm²

Wire, Straight, Stainless Steel, Unplated Plating, Strip/Reel, Open Barrel

[View on TE.com >](#)

Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **.26 – .33 mm²**

Terminal Orientation: **Straight**

Contact Base Material: **Stainless Steel**

Features

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Contact Features

Quick Disconnect Terminal Type	Tab
Terminal Orientation	Straight
Contact Base Material	Stainless Steel
Terminal Plating Material	Unplated
Barrel Type	Open

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Product Length	15.24 mm[.6 in]
Terminal Material Thickness	.2 mm[.008 in]
Wire Size	.26 – .33 mm ²



Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 250 °C[-40 – 482 °F]

Packaging Features

Packaging Quantity	10000
Packaging Method	Strip/Reel

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 2150629-1
OCEAN_2.0_Applicator-E-050F-REM



KIT
TE Part # 7-2150629-7
OCEAN_2.0_SPARE_PART_KIT-050F




TE Part # 61148-1
BRUSH HOLDER AMPLIVAR 22-17 AWG PHBZ



TE Part # 63257-1
CONTACT TERMINAL 22-18 AWG TPBR



TE Part # 2150629-2
OCEAN_2.0_Applicator-E-050F-REA




TE Part # 63701-1
WELD TAB 20-16 AWG NPSTL



TE Part # 62009-1
BRUSH CONTACT TAB 20-14 AWG PHBZ



TE Part # 62153-1
WELD TAB 20-16 AWG TPSTL



TE Part # 63257-2
CONTACT TERMINAL 22-18 AWG TPBR



TE Part # 62008-1
BRUSH CONTACT TAB 20-14 AWG PHBZ


Customers Also Bought



TE Part #335276-000
TTVF150WE-100




TE Part #5414710001
TMS-SCE-1-1/2-2.0-9



TE Part #878509-000
202K174-25-02-0




TE Part #102241-5
07 MODIV HSG COMP SR .100 POL




TE Part #696010-2
SPLICE BUTT PG 16-14/22-18



TE Part #5-1393252-6
W67-X2Q12-15=M6/M7/M9/W6/W7




TE Part #2-1474644-1
FSN-21A-8



TE Part #9-2176480-3
RA73F 1J 4K99 0.1% 5K RL



TE Part #E32547-000
TTVF150VT-100



TE Part #469766-1
BUSHING, FLYWHEEL REPLACEMENT

Documents

Product Drawings

WELD TAB 24-22 AWG SST

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_62827-1_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_62827-1_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_62827-1_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.