



DIMENSIONS:

A	4.375" ±0.063
B	5.096" ±0.125
C	5.300" ±0.063
D	3.500" ±0.063
E	3.500" ±0.063
G	0.281" x 0.625" ±0.015



NOTE: ALL LEADS 8" OUT MIN.



ELECTRICAL DATA:

TESTS	CONDITIONS	ACCEPTANCE CRITERIA	
I _{ex}	@ 120V, 60Hz, WHT - BLK	400mA	Max.
Sec. N.L.V	@ 120V, 60Hz, WHT - BLK		
	RED - RED =	676.7V	±2%
	RED - RED/YEL = RED/YEL - RED =	338.4V	±2%
	RED/YEL - VIO =	52.46V	±2%
	YEL - YEL =	5.246V	±2%
	YEL - YEL/BLK = YEL/BLK - YEL =	2.623V	±2%
	GRN - GRN =	6.557V	±2%
	GRN - GRN/YEL = GRN/YEL - GRN =	3.279V	±2%
DCR	@ 20°C, WHT - BLK =	1.050 Ω	±20%
	@ 20°C, BRN - BLU =	1.137 Ω	±20%
	@ 20°C, RED - RED =	28.60 Ω	±20%
	@ 20°C, YEL - YEL =	0.019 Ω	±20%
	@ 20°C, GRN - GRN =	0.012 Ω	±20%
HIPOT	PRIMARY - SECONDARY	2500V, 60Hz, 1 SEC	

HAMMOND
MANUFACTURING

ELECTRONIC DIVISION

52 RANKIN PLACE,
WATERLOO, ONTARIO, N2J 3Z5

PH # (519) 886-6181
FAX # (519) 886-9540

DWG. BY: C. ILIE
DATE: 01/19/10

CHK'D BY:
APP'D. BY:
DIMENSIONS: IN(X) MM()

TITLE: POWER
TRANSFORMER

DWG. NO.
373FX