




REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	OCT.08/15	L.CHAN



LED SCHEMATIC



NOTES:

1. MATERIALS
- HOUSING: HIGH TEMPERATURE THERMOPLASTIC.
- CONTACTS: COLOUR: BLACK. FLAMMABILITY RATING UL 94V-0
- PLATING: PHOSPHOR BRONZE
- GOLD PLATING ON MATING AREA REFER TO THE AMPHENOL PART NO.
- 50 μ" [1.27 MICRONS]
- MIN. NICKEL UNDERPLATE
- 100 μ" [2.54 MICRONS]
- MIN. MATTE-TIN OR GOLD FLASH ON CONTACT TAILS.
- SHIELD: COPPER ALLOY
- PLATING: NICKEL

RECOMMENDED SOLDERING TEMPERATURE

WAVE SOLDERING PEAKED AT 265°C MAX FOR 10 SECOND MAX.

AMPHENOL PART NUMBER

RJSNE-X38X-08X


GOLD PLATING REFER TO LED OPTIONS

D = 6u" DRAWING FOR ORDERING CODES


G = 15u"

J = 30u"

5 = 50u"



(COMPONENT SIDE OF BOARD)



UNLESS SPECIFIED OTHERWISE	DRAWN Jack Guo	OCT08/15
PRIMARY UNITS: INCHES	CHECKED	
SECONDARY: MILLIMETERS	M.E. APP'D	
	Q.A. APP'D	
	DWG APP'D L.CHAN	OCT08/15
	ENG. REL. NO.	
1 DECIMAL PLACE	REF.	
2 DECIMAL PLACES	THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING
3 DECIMAL PLACES		
ANGULAR DEGREES ±.015		

Amphenol Canada Corp. www.amphenolcanada.com			
STACKABLE MODULAR JACK 2X4 PORTS, 8 POSITIONS, 8 CONTACTS, WITH LEDS, SHIELDED, TRAY PACKAGING -RoHS COMPLIANT			
DWG NO.	P-RJSNE-X38X-08X		REV A
CODE ID NO. 03554	DWG SIZE	SCALE	SHEET 1 OF 1