





APPROVED: _____
DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT



Positions: 2 thru 20
A = .156 [3.96] x No. of Positions
B = .156 [3.96] x No. of Spaces

SPECIFICATIONS:
Material:
Insulator: PA66, glass reinforced, rated UL 94V-2
Insulator color: White
contact: Brass, Tin or Ni plated
Electrical:
Current rating: 7 Amps max
Contact resistance: 20mohms max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Temperature Rating:
Operating temperature: -40°C to +85°C
Environmental:

Lead free, RoHS compliant



Rev	AWO #	Description	Date	Appr
-		RELEASED	6/18/10	
A		ECN	12/8/10	
B		REVISED DIM.	2/17/14	AY/MY

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES		ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
.X ± .10 .XX ± .020 .XXX ± .015 .XXX ± .010	ØXX ± .10 ØXXX ± .015 ØXXX ± .010	TITLE .156 [3.96] HEADER, RIGHT ANGLE	
APPROVALS	DATE	PART NO. LHD-XX-TRA	
DRAWN	DY	SIZE X	
CHECKED		REV. B	
APPROVED		REF: S00019C SCALE: NTS SHEET 1 OF 1	