

# IGBT - Shorted-Anode

1300 V, 30 A

## FGH30S130P

### Description

Using advanced field stop trench and shorted-anode technology, ON Semiconductor's shorted-anode trench IGBTs offer superior conduction and switching performances for soft switching applications. The device can operate in parallel configuration with exceptional avalanche capability. This device is designed for induction heating and microwave oven.

### Features

- High Speed Switching
- Low Saturation Voltage:  $V_{CE(sat)} = 1.75$  V @  $I_C = 30$  A
- High Input Impedance
- This Device is Pb-Free and is RoHS Compliant



### Applications

- Induction Heating, Microwave Oven




ON Semiconductor®

[www.onsemi.com](http://www.onsemi.com)



TO-247-3LD  
CASE 340CK

### MARKING DIAGRAM



\$Y	= ON Semiconductor Logo
&Z	= Assembly Plant Code
&3	= Numeric Date Code
&K	= Lot Code
FGH30S130P	= Specific Device Code

### ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

ABSOLUTE MAXIMUM RATINGS ( $T_C = 25^\circ\text{C}$  unless otherwise noted)

Description		Symbol	Rating	Unit
Collector to Emitter Voltage		$V_{CES}$	1300	V
Gate to Emitter Voltage		$V_{GES}$	$\pm 25$	V
Collector Current	$T_C = 25^\circ\text{C}$	$I_C$	60	A
Collector Current	$T_C = 100^\circ\text{C}$		30	A
Pulsed Collector Current (Note 1)		$I_{CM}$	90	A
Diode Continuous Forward Current	$T_C = 25^\circ\text{C}$	$I_F$	60	A
Diode Continuous Forward Current	$T_C = 100^\circ\text{C}$		30	A
Maximum Power Dissipation	$T_C = 25^\circ\text{C}$	$P_D$	500	W
Maximum Power Dissipation	$T_C = 100^\circ\text{C}$		250	W
Operating Junction Temperature		$T_J$	-55 to +175	$^\circ\text{C}$
Storage Temperature Range		$T_{stg}$	-55 to +175	$^\circ\text{C}$
Maximum Lead Temp. for soldering Purposes, 1/8" from case for 5 seconds		$T_L$	300	$^\circ\text{C}$

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Limited by  $T_{jmax}$ .

## THERMAL CHARACTERISTICS

Parameter	Symbol	Typ	Max	Unit
Thermal Resistance, Junction to Case, Max	$R_{\theta JC}(\text{IGBT})$	-	0.3	$^\circ\text{C}/\text{W}$
Thermal Resistance, Junction to Ambient, Max	$R_{\theta JA}$	-	40	$^\circ\text{C}/\text{W}$

## PACKAGE MARKING AND ORDERING INFORMATION

Part Number	Top Mark	Package	Reel Size	Tape Width	Quantity
FGH30S130P	FGH30S130P	TO-247	-	-	30

ELECTRICAL CHARACTERISTICS OF THE IGBT ( $T_C = 25^\circ\text{C}$  unless otherwise noted)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
-----------	--------	-----------------	-----	-----	-----	------

## OFF CHARACTERISTICS

Collector Cut-Off Current	$I_{CES}$	$V_{CE} = 1300$ , $V_{GE} = 0$ V	-	-	1	mA
G-E Leakage Current	$I_{GES}$	$V_{GE} = V_{GES}$ , $V_{CE} = 0$ V	-	-	$\pm 500$	nA

## ON CHARACTERISTICS

Collector Cut-Off Current	$I_{CES}$	$V_{CE} = 1300$ , $V_{GE} = 0$ V	-	-	1	mA
G-E Leakage Current	$I_{GES}$	$V_{GE} = V_{GES}$ , $V_{CE} = 0$ V	-	-	$\pm 500$	nA
Collector Current	$I_C$	$V_{CE} = 1300$ , $V_{GE} = 0$ V	4.5	6.0	7.5	V
Collector Current	$I_C$	$V_{CE} = 1300$ , $V_{GE} = 15$ V, $T_C = 25^\circ\text{C}$	-	1.75	2.3	V
Collector Current	$I_C$	$V_{CE} = 1300$ , $V_{GE} = 15$ V, $T_C = 125^\circ\text{C}$	-	1.85	-	V
Collector Current	$I_C$	$V_{CE} = 1300$ , $V_{GE} = 15$ V, $T_C = 175^\circ\text{C}$	-	1.9	-	V
Diode Forward Voltage	$V_{FDM}$	$I_F = 30$ A, $T_C = 25^\circ\text{C}$	-	1.7	2.2	V
Diode Forward Voltage	$V_{FDM}$	$I_F = 30$ A, $T_C = 175^\circ\text{C}$	-	2.1	-	V

# FGH30S130P

## ELECTRICAL CHARACTERISTICS OF THE IGBT ( $T_C = 25^\circ\text{C}$ unless otherwise noted) (continued)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
<b>DYNAMIC CHARACTERISTICS</b>						
Input Capacitance	$C_{ies}$	$V_{CE} = 30\text{ V}$ , $V_{GE} = 0\text{ V}$ , $f = 1\text{ MHz}$	–	3345	–	pF
Output Capacitance	$C_{oes}$		–	75	–	pF
Reverse Transfer Capacitance	$C_{res}$		–	60	–	pF
<b>SWITCHING CHARACTERISTICS</b>						
Turn-On Delay Time	$t_{d(on)}$	$V_{CC} = 600\text{ V}$ , $I_C = 30\text{ A}$ , $R_G = 10\text{ }\Omega$ , $V_{GE} = 15\text{ V}$ , Resistive Load, $T_C = 25^\circ\text{C}$	–	39	–	ns
Rise Time	$t_r$		–	360	–	ns
Turn-Off Delay Time	$t_{d(off)}$		–	620	–	ns
Fall Time	$t_f$		–	160	210	ns
Turn-On Switching Loss	$E_{on}$		–	1.3	–	mJ
Turn-Off Switching Loss	$E_{off}$		–	1.22	1.6	mJ
Total Switching Loss	$E_{ts}$		–	2.52	–	mJ
Turn-On Delay Time	$t_{d(on)}$	$V_{CC} = 600\text{ V}$ , $I_C = 30\text{ A}$ , $R_G = 10\text{ }\Omega$ , $V_{GE} = 15\text{ V}$ , Resistive Load, $T_C = 175^\circ\text{C}$	–	38	–	ns
Rise Time	$t_r$		–	375	–	ns
Turn-Off Delay Time	$t_{d(off)}$		–	635	–	ns
Fall Time	$t_f$		–	270	–	ns
Turn-On Switching Loss	$E_{on}$		–	1.59	–	mJ
Turn-Off Switching Loss	$E_{off}$		–	1.78	–	mJ
Total Switching Loss	$E_{ts}$		–	3.37	–	mJ
Total Gate Charge	$Q_g$	$V_{CE} = 600\text{ V}$ , $I_C = 30\text{ A}$ , $V_{GE} = 15\text{ V}$	–	372.3	–	nC
Gate to Emitter Charge	$Q_{ge}$		–	18.7	–	nC
Gate to Collector Charge	$Q_{gc}$		–	156.2	–	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

## TYPICAL PERFORMANCE CHARACTERISTICS




Figure 1. Typical Output Characteristics




Figure 2. Typical Output Characteristics




Figure 3. Typical Saturation Voltage Characteristics




Figure 4. Transfer Characteristics




Figure 5. Saturation Voltage vs. Case Temperature at Variant Current Level




Figure 6. Saturation Voltage vs. Vge

## TYPICAL PERFORMANCE CHARACTERISTICS (continued)



Figure 7. Saturation Voltage vs.  $V_{GE}$ 

Figure 8. Capacitance Characteristic




Figure 9. Gate Charge Characteristics




Figure 10. SOA Characteristics




Figure 11. Turn-On Characteristics vs. Gate Resistance




Figure 12. Turn-Off Characteristics vs. Gate Resistance

## TYPICAL PERFORMANCE CHARACTERISTICS (continued)




Figure 13. Turn-On Characteristics vs. Collector Current




Figure 14. Turn-Off Characteristics vs. Collector Current




Figure 15. Switching Loss vs. Gate Resistance




Figure 16. Switching Loss vs. Collector Current




Figure 17. Turn-Off Switching SOA Characteristics







Figure 18. Forward Characteristics

**TYPICAL PERFORMANCE CHARACTERISTICS** (continued)**Figure 19. Transient Thermal Impedance of IGBT**

TO-247-3LD SHORT LEAD  
CASE 340CK  
ISSUE A



DATE 31 JAN 2019

NOTES: UNLESS OTHERWISE SPECIFIED.

- A. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
- B. ALL DIMENSIONS ARE IN MILLIMETERS.
- C. DRAWING CONFORMS TO ASME Y14.5 - 2009.
- D. DIMENSION A1 TO BE MEASURED IN THE REGION DEFINED BY L1.
- E. LEAD FINISH IS UNCONTROLLED IN THE REGION DEFINED BY L1.

**GENERIC  
MARKING DIAGRAM\***



XXXX = Specific Device Code  
A = Assembly Location  
Y = Year  
WW = Work Week  
ZZ = Assembly Lot Code

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "■", may or may not be present. Some products may not follow the Generic Marking.

DIM	MILLIMETERS		
	MIN	NOM	MAX
A	4.58	4.70	4.82
A1	2.20	2.40	2.60
A2	1.40	1.50	1.60
b	1.17	1.26	1.35
b2	1.53	1.65	1.77
b4	2.42	2.54	2.66
c	0.51	0.61	0.71
D	20.32	20.57	20.82
D1	13.08	~	~
D2	0.51	0.93	1.35
E	15.37	15.62	15.87
E1	12.81	~	~
E2	4.96	5.08	5.20
e	~	5.56	~
L	15.75	16.00	16.25
L1	3.69	3.81	3.93
ØP	3.51	3.58	3.65
ØP1	6.60	6.80	7.00
Q	5.34	5.46	5.58
S	5.34	5.46	5.58

DOCUMENT NUMBER:	98AON13851G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	TO-247-3LD SHORT LEAD	PAGE 1 OF 1

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

**onsemi**, **ONSEMI**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)

