





PRODUCT NUMBER	PITCH
YK224xx0x0J0G	6.35 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW



MATERIALS & ELECTRICAL	cULus	CQC
RATED VOLTAGE & CURRENT:	250 V, 10 A	250 V, 9 A
WITHSTAND VOLTAGE:	AC 2000 V/Min	
INSULATION RESISTANCE:	1000 MΩ OR MORE AT DC 500 V	
OPERATING TEMPERATURE RANG:	-40 °C ~ +115 °C	
SCREW TORQUE VALUE:	5.3 Lb-In.	
WIRE RANGE:	22 - 18 AWG	
1) HOUSING:	Thermoplastic, UL 94 V-0 BLACK	
2) TERMINAL:	BRASS, 0.8t	
3) TERMINAL SCREWS:	STEEL, M3	
APPROVAL:		

DIMENSION

Dim A	N×6.35±1.0
Dim B	(N-1)×6.35

N=Number of poles

Poles	Tolerance
2p-5p	±0.20
6p-10p	±0.25
11p-16p	±0.35
17p-24p	±0.40
25p-31p	±0.50

PART NO.: YK 224xx 0 x 0 J0G

No. of poles
02 2 poles
03 3 poles
...
31 31 poles

Plated

Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection 	product family TERMINAL BLOCK			
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM	title TERMINAL BLOCK			
				angles	X.±0.5		BARRIER TYPE			
				total	X.X±0.3		dwg no			
				X'±1"	X.XX±0.1	scale	sheet 1 of 1			
				dr	EVAN LU	061614	size			
				enr	EVAN LU	061614	YK224xx0x0J0G			
				chr	HANKE FENG	061614	A4			
				appd	SHI JUN	061614	type			
sheet index		revision sheet	A				CUSTOMER Drawing			
		1								