

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P1	PART OBSOLESCENCE	05AUG2024	AR	VG

POS. "n"	"L"	PART NUMBER
2	4.58	-2-
3	7.12	826468 -3
4	9.66	-4-
5	12.20	-5-
6	14.74	-6-
7	17.28	-7-
8	19.82	-8-
9	22.36	-9-
10	24.90	1- -0
11	27.44	1- -1-
12	29.98	1- -2-
13	32.52	1- -3-
14	35.06	1- -4-
15	37.60	1- -5-
16	40.14	1- -6-
17	42.68	1- -7-
18	45.22	1- -8-
19	47.76	1- -9-
20	50.30	2- -0-
21	52.84	2- -1-
22	55.38	2- -2-
23	57.92	2- -3-
24	60.46	2- -4-
25	63.00	2- -5-
26	65.54	2- -6-
27	68.08	2- -7-
28	70.62	2- -8-
29	73.16	2- -9-
30	75.70	3- -0-
31	78.24	3- -1-
32	80.78	3- -2-
33	83.32	3- -3-
34	85.86	3- -4-
35	88.40	3- -5-
36	90.94	3- -6-
37	93.48	3- -7-
38	96.02	3- -8-
39	98.56	3- -9-
40	101.10	4- -0-
41	103.64	4- -1-
42	106.18	4- -2-
43	108.72	4- -3-
44	111.26	4- -4-
45	113.80	4- -5-
46	116.34	4- -6-
47	118.88	4- -7-
48	121.42	4- -8-
49	123.96	4- -9-
50	126.50	5- 826468 -0


 OBSOLETE

SEE DIAGRAM
826467 SHEET 1 OF 2
(DIN A2)

TE Connectivity. All Rights Reserved.



THERE IS NO ORIGINAL OF THIS DRAWING

DIMENSIONS: mm	DWN —	MATERIAL —	FINISH —
TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK —	 TE Connectivity	
0 PLC ± —	APVD —		
1 PLC ± —	PRODUCT SPEC —		
2 PLC ± —	APPLICATION SPEC —	NAME AMPMODU II STIFTLEISTE 90DEG EINREIHIG	
3 PLC ± —	WEIGHT —	SIZE A4	CAGE CODE 00779
4 PLC ± —		DRAWING NO C-826468	RESTRICTED TO —
ANGLES ± —	CUSTOMER DRAWING		
	SCALE —	SHEET 1 of 1	REV P1