

## Competitor Cross Reference



% can be used as a wildcard in search

## Heyco® Nylon Cable Clamps



### Part Numbers and Specifications

### Features

MOUNTING HOLE DIAMETER		SCREW SIZE	PART DIMENSION A		PART NO. V-2*		DESCRIPTION	CENTER-TO-CENTER DIMENSION B		CAD
in.	mm.		in.	mm.	Black	Natural		in.	mm.	
<b>Light Duty - 3/8" (9,5 mm) Wide, .05" (1,3 mm) Thick</b>										
.170	4,3	8	.125	3,2	<a href="#">3362</a>	<a href="#">3312</a>	CCL 125-170	.36	9,1	<a href="#">CAD</a>
			.187	4,7	<a href="#">3363</a>	<a href="#">3313</a>	CCL 187-170	.39	9,9	<a href="#">CAD</a>
			.250	6,3	<a href="#">3364</a>	<a href="#">3314</a>	CCL 250-170	.42	10,7	<a href="#">CAD</a>
			.312	7,9	<a href="#">3365</a>	<a href="#">3315</a>	CCL 312-170	.46	11,7	<a href="#">CAD</a>
			.375	9,5	<a href="#">3366</a>	<a href="#">3316</a>	CCL 375-170	.49	12,4	<a href="#">CAD</a>
			.437	11,1	<a href="#">3367</a>	<a href="#">3317</a>	CCL 437-170	.53	13,5	<a href="#">CAD</a>
			.500	12,7	<a href="#">3368</a>	<a href="#">3318</a>	CCL 500-170	.55	14,0	<a href="#">CAD</a>
.203	5,2	10	.125	3,2	<a href="#">3352</a>	<a href="#">3302</a>	CCL 1/8	.34	8,6	<a href="#">CAD</a>
			.187	4,7	<a href="#">3353</a>	<a href="#">3303</a>	CCL 3/16	.38	9,7	<a href="#">CAD</a>
			.250	6,3	<a href="#">3354</a>	<a href="#">3304</a>	CCL 1/4	.41	10,4	<a href="#">CAD</a>
			.312	7,9	<a href="#">3355</a>	<a href="#">3305</a>	CCL 5/16	.44	11,2	<a href="#">CAD</a>
			.375	9,5	<a href="#">3356</a>	<a href="#">3306</a>	CCL 3/8	.48	12,2	<a href="#">CAD</a>
			.437	11,1	<a href="#">3357</a>	<a href="#">3307</a>	CCL 7/16	.51	13,0	<a href="#">CAD</a>
			.500	12,7	<a href="#">3358</a>	<a href="#">3308</a>	CCL 1/2	.53	13,5	<a href="#">CAD</a>
<b>Heavy Duty - 1/2" (12,7 mm) Wide, .06" (1,5 mm) Thick</b>										
.203	5,2	10	.125	3,2	<a href="#">3372</a>	<a href="#">3322</a>	CCH 1/8	.37	9,4	<a href="#">CAD</a>
			.187	4,8	<a href="#">3373</a>	<a href="#">3323</a>	CCH 3/16	.41	10,4	<a href="#">CAD</a>
			.250	6,3	<a href="#">3374</a>	<a href="#">3324</a>	CCH 1/4	.44	11,2	<a href="#">CAD</a>
			.312	7,9	<a href="#">3375</a>	<a href="#">3325</a>	CCH 5/16	.48	12,2	<a href="#">CAD</a>
			.375	9,5	<a href="#">3376</a>	<a href="#">3326</a>	CCH 3/8	.51	13,0	<a href="#">CAD</a>
			.437	11,1	<a href="#">3377</a>	<a href="#">3327</a>	CCH 7/16	.54	13,7	<a href="#">CAD</a>
			.500	12,7	<a href="#">3378</a>	<a href="#">3328</a>	CCH 1/2	.58	14,7	<a href="#">CAD</a>
			.562	14,3	<a href="#">3379</a>	<a href="#">3329</a>	CCH 9/16	.61	15,5	<a href="#">CAD</a>
			.625	15,9	<a href="#">3380</a>	<a href="#">3330</a>	CCH 5/8	.65	16,5	<a href="#">CAD</a>
			.687	17,4	<a href="#">3381</a>	<a href="#">3331</a>	CCH 11/16	.68	17,3	<a href="#">CAD</a>
			.750	19,1	<a href="#">3382</a>	<a href="#">3332</a>	CCH 3/4	.71	18,0	<a href="#">CAD</a>
			.812	20,6	<a href="#">3383</a>	<a href="#">3333</a>	CCH 13/16	.75	19,1	<a href="#">CAD</a>
			.875	22,2	<a href="#">3384</a>	<a href="#">3334</a>	CCH 7/8	.78	19,8	<a href="#">CAD</a>
			1.000	25,4	<a href="#">3390</a>	<a href="#">3340</a>	CCH 1	.85	21,6	<a href="#">CAD</a>
			1.125	28,6	<a href="#">3392</a>	<a href="#">3342</a>	CCH 1-1/8	.92	23,4	<a href="#">CAD</a>
			1.187	30,1	<a href="#">3393</a>	<a href="#">3343</a>	CCH 1-3/16	.95	24,1	<a href="#">CAD</a>
			1.250	31,8	<a href="#">3394</a>	<a href="#">3344</a>	CCH 1-1/4	.99	25,1	<a href="#">CAD</a>
1.375	34,9	<a href="#">3396</a>	<a href="#">3346</a>	CCH 1-3/8	1.05	26,7	<a href="#">CAD</a>			
1.500	38,1	<a href="#">3398</a>	<a href="#">3348</a>	CCH 1-1/2	1.12	28,4	<a href="#">CAD</a>			
<b>Adjustable - 1/2" (12,7 mm) Wide, .065" (1,7mm) Thick</b>										
.203	5,2	10	1.75 - 2.00	44,5 - 50,8	-	<a href="#">3755</a>	ACC 1750-2000			

Standard colors black and natural.

\*Consult Heyco for V-0 parts (not shown)

