


Pxxx0S3H Series

High Surge Current SIDACtor® - DO-214AB



Schematic Symbol



Applicable Global Standards

- TIA-968-A
- TIA-968-B
- ITU K.20/21 enhanced level
- ITU K.20/21 basic level
- GR 1089 intra-building
- IEC 61000-4-5, 2nd edition
- YD/T 1082
- YD/T 993
- YD/T 950

Description

The Pxxx0S3H series DO-214AB protection thyristors are components designed to protect equipment located in hostile environments from overvoltage transients.

The Pxxx0S3H series protect exposed interfaces in industrial and ICT applications, such as RS-485 data interfaces, AC or DC power supplies. These components' switching voltage V_s are much lower than alternative Gas Discharge Tubes (GDT), and on-state voltage V_T are much lower than alternative GDTs, Metal Oxide Varistors (MOV) and TVS Diodes.

This Pxxx0S3H series are rated 2000 A 8/20 μ s, enabling equipment compliance with regulatory and customer surge requirements.

Features and Benefits

- High surge rating 8/20 μ s 2000 A protection
- Component properties do not degrade after multiple surge events within its limits
- SMD low profile surface mount package minimizing PCB footprint
- Low voltage overshoot
- Low on-state voltage
- Typical failure mode is short from over-specified voltage or current
- Whisker test is conducted based on JEDEC JESD201A per its table 4a and 4c passclass 1/2
- IEC 61000-4-2 ESD 30 kV(Air), 30 kV (Contact)
- Recognized compound meeting flammability rating UL94V-0
- RoHS compliant and halogen-free
- Pb-free E3 means 2nd level interconnect is Pb-free and the terminal finish material is tin (Sn) (IPC/JEDEC J-STD609A.01)

Electrical Characteristics

Part Number	Marking	V_{DRM} @ $I_{DRM} = 5 \mu A$	V_s @ 100 V/ μ s	I_H	I_s	I_T	V_T @ $I_T = 2.2 A$	Capacitance @ 1 MHz, 2 V bias	
		V min	V max	mA min	mA max	A max	V max	pF typ	pF max
P0640S3HLRP	P06H	58	77	50	800	2.2	4	150	550
P0720S3HLRP	P07H	65	88	50	800	2.2	4	150	550
P0900S3HLRP	P09H	75	98	50	800	2.2	4	150	550
P1100S3HLRP	P11H	90	130	50	800	2.2	4	150	450
P1300S3HLRP	P13H	120	160	50	800	2.2	4	150	450
P1500S3HLRP	P15H	140	180	50	800	2.2	4	150	450
P1900S3HLRP	P19H	155	220	50	800	2.2	4	150	450
P2300S3HLRP	P23H	180	260	50	800	2.2	4	150	450
P2600S3HLRP	P26H	220	300	50	800	2.2	4	150	450
P3100S3HLRP	P31H	275	350	50	800	2.2	4	150	450
P3500S3HLRP	P35H	320	400	50	800	2.2	4	150	450
P3800S3HLRP	P38H	350	430	50	800	2.2	4	150	450

Notes:

- Absolute maximum ratings measured at $T_A = 25^\circ C$ (unless otherwise noted).
- Components are bi-directional (unless otherwise noted).

Pxxx0S3H Series

High Surge Current SIDACtor® - D0-214AB

Surge Ratings

Series	I_{PP}	I_{TSM} 50 / 60 Hz	di/dt
	8/20 ¹ 1.2/50 ²		
	A min	A min	A/μs max
H	2000	250	1000

Notes:


1. Current waveform in μs
2. Voltage waveform in μs

- Peak pulse current rating (I_{PP}) is repetitive and guaranteed for the life of the product.
- I_{PP} ratings applicable over temperature range of -40 °C to +85 °C
- The device must initially be in thermal equilibrium with -40 °C ≤ T_J ≤ +150 °C


Thermal Considerations

Package	Symbol	Parameter	Value	Unit
DO-214AB 	T_J	Operating Junction Temperature Range	-65 to +125	°C
	T_S	Storage Temperature Range	-65 to +150	°C
	$R_{\theta JA}$	Thermal Resistance: Junction to Ambient	75	°C/W


V-I Characteristics




Typical Surge Response (8/20 μs)



Normalized V_S Change vs. Junction Temperature



Normalized DC Holding Current vs. Case Temperature




Pxxx0S3H Series

High Surge Current SIDACtor® - D0-214AB

Soldering Parameters

Reflow Condition		Pb-free assembly (see Fig 1)
Pre Heat	- Temperature Min ($T_{s(min)}$)	+150 °C
	- Temperature Max ($T_{s(max)}$)	+200 °C
	- Time (Min to Max) (t_s)	60-120 secs
Average Ramp Up Rate (Liquidus Temp (T_L) to Peak)		3 °C/sec max
$T_{s(max)}$ to T_L - Ramp-up Rate		3 °C/sec max
Reflow	- Temperature (T_L) (Liquidus)	+217 °C
	- Temperature (t_L)	60-150 secs
Peak Temp (T_p)		+260(+0/-5)°C
Time Within 5°C of Actual Peak Temp (t_p)		30 secs max
Ramp-Down Rate		6 °C/sec max
Time 25°C to Peak Temp (T_p)		8 min max
Do Not Exceed		+260 °C




Physical Specifications

Weight	0.009 ounce, 0.266 grams
Case	JEDEC DO-214AA. Molded component over glass passivated junction
Terminal	Matte tin-plated leads, solderable per JESD22-B102


Environmental Specifications

High Temp Voltage Blocking	80 % rated V_{DRM} (V_{AC} Peak) +125 °C, 504 or 1008 hrs. MIL-STD-750 (Method 1040) JEDEC, JESD22-A-101
Temp Cycling	-65 °C to +150 °C, 15 min. dwell, 10 up to 100 cycles. MIL-STD-750 (Method 1051) EIA/JEDEC, JESD22-A104
Biased Temp & Humidity	52 V_{DC} (+85 °C) 85 %RH, 504 up to 1008 hrs. EIA/JEDEC, JESD22-A-101
High Temp Storage	+150 °C 1008 hrs. MIL-STD-750 (Method 1031) JEDEC, JESD22-A-101
Low Temp Storage	-65 °C, 1008 hrs.
UAHST	96 hours at $T_A = 130$ °C/85 %RH. JEDEC, JESD22-A-101
Resistance to Solder Heat	+260 °C, 30 secs. MIL-STD-750 (Method 2031)
Moisture Sensitivity Level	85 %RH, +85 °C, 168 hrs., 3 reflow cycles (+260 °C Peak). JEDEC-J-STD-020, Level 1

Part Numbering



Part Marking




YMXXX - Trace Code Marking

Y - Year code

M - Month Code


XXX - Lot Code

Pxxx0S3H Series**High Surge Current SIDACtor® - DO-214AB****Dimensions****Recommended Soldering pad layout**

Dimensions	Inches		Millimeters	
	Min	Max	Min	Max
A	0.114	0.126	2.900	3.200
B	0.260	0.280	6.600	7.110
C	0.220	0.245	5.590	6.220
D	0.079	0.103	2.060	2.620
E	0.030	0.060	0.760	1.520
F	-	0.008	-	0.203
G	0.305	0.320	7.750	8.130
H	0.006	0.012	0.152	0.305
I	0.129	-	3.300	-
J	0.094	-	2.400	-
K	-	0.165	-	4.200
L	0.094	-	2.400	-

Packing Options

Part number	Component Package	Quantity	Packaging Option	Packaging Specification
Pxxx0S3HLRP	DO-214AB	3000	Tape & Reel - 16 mm tape/13" reel	EIA STD RS-481

Tape and Reel Specification

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.