





APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/29/13	
A		REVISED PART NO.	1/16/14	HR
B		UPDATE SPEC.	1/29/15	AY/CH



#### SPECIFICATIONS:

##### Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Green

Screw: Steel, M2.5/Zinc plated

Cage: Brass, Tin plated

Pin Header: Brass, Tin plated

##### Electrical:

Operation voltage: UL: 300V max, IEC: 250V max

Current rating: UL: 15 Amps max, IEC: 17.5 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min @ 500 VDC

Dielectric withstanding voltage: 2000 VAC for 1 minute

##### Mechanical:

Wire range: 30-14AWG, 1.5mm<sup>2</sup>

Torque: 0.4N-m, 3.6Lb-in

Strip Length: 6-7mm

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



Positions: 2 thru 24

A = .200 [5.08] x No. of Positions

B = .200 [5.08] x No. of Spaces

UNLESS OTHERWISE SPECIFIED  
 ALL DIMENSIONS ARE INCHES [MM]  
 TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	AY	8/29/13
CHECKED	AH	8/29/13
APPROVED		

## ADAM TECH

909 Rahway Avenue, Union, NJ 07083  
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE  
 TERMINAL BLOCK, .200 [5.08] PITCH

SIZE X	PART NO. EBVA-XX-D	REV. B
REF: S00067C	SCALE: NTS	SHEET 1 OF 1