



Part Number : 845860017

Product Description : Micro-Change (M12) Tee, 5 Pole, Two Female, One Male, meets NMEA 2000

Series Number : 84586

Status : Active

Product Category : Industrial Tees and Splitters

Engineering Number : NMEA-MICT555

Documents & Resources

Drawings

Drawing 845860017_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	84586
Description	Micro-Change (M12) Tee, 5 Pole, Two Female, One Male, meets NMEA 2000
IP Rating	IP67
Product Family	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Type	Drop Tee
UPC	822350898270

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	N/A

Physical

Color - Cable Jacket	Gray
Drop Connector	Micro-Change (M12)
Drop Gender	Female
Keyway	Single
LED Indicator	No
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Net Weight	266.000/g
Poles	5
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Male

Temperature Range - Operating	0°C to +60°C
-------------------------------	--------------

This document was generated on Jul 31, 2024