




## HEAT SHRINK BOOTS



✓ Active

TE CONNECTIVITY (TE)

202A174-3/42-0

Raychem | CAP , CRPS

202A174-3/42-0

TE Internal Number: 814729-000

Alias ID: 1196347-9

EU RoHS Compliant

EU ELV Compliant

Lipped No

Operating Temperature Range (°C) -20 – 60

Fluid/Chemical Resistance Suitable for occasional exposure to fluids

Adhesive Options /42 Precoat, -20 – 60°C (-4 – 140°F)

Material Systems Code 10

### PRODUCT DRAWING

English

## DOCUMENTATION

Product Drawings

**Boot, Straight, Overexpanded**

PDF

English

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

**Molded Part Type** Molded Boot

## Configuration Features

**Lipped** No

---

## Body Features

**Material Systems Code** 10

**Adhesive Pre-Coat** Yes

**Material** Modified Polyolefin

---

## Dimensions

**Cable Diameter Range** 16 – 48.3 mm [.63 – 1.9 in]

**Wire/Cable Outside Diameter** .7 in, .71 in, .787 in, .87 in, .9 in, .94 in, 1 in, 1.02 in, 1.1 in, 18 mm, 20 mm, 22 mm, 24 mm, 26 mm, 28 mm

---

## Usage Conditions

**Operating Temperature Range (°C)** -20 – 60

---

## Operation/Application

**Power Cable Accessory** No

---

## Industry Standards

**Government Qualified** No

**Approved Standards** BS-G-198-5-DA, DEF Std 59-97 Issue 3 Type DA, SAE AS I 81765/1, Type I, UL 224, File E85381

---

## Other

**Fluid/Chemical Resistance** Suitable for occasional exposure to fluids

**Adhesive Options** /42 Precoat, -20 – 60°C (-4 – 140°F)

**Adhesive Type** General Purpose Pre-Coat Adhesive

## Statement of Compliance

### **Statement of Compliance**

PDF

---