


[PRODUCTS](#)
[INDUSTRIES](#)
[CAPABILITIES](#)
[CAREERS](#)
[RESOURCES](#)
[Register](#) [Login](#)
[CONTACT MOLEX](#)
[FIND DISTRIBUTOR](#)


[Product Name Index](#)

[Cross Reference](#)
[Home:](#) >

Part Number: 173109-0510
FCT DSUB STR PC RCPT 15 PN W/JACKPOST

Image not available

Status: Active
Series: [173109](#)
Category: Molex Parts
EngineeringOldPN: F15S1G2-1426

[Go to Part Detail](#) ▼

Series image - Reference only

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

EU ELV: Not Relevant

EU RoHS: Not Reviewed

EU RoHS Phthalates: Not Reviewed

China RoHS: Not Reviewed

REACH SVHC: Not Reviewed

Low-Halogen Status: Not Reviewed



Product Compliance Statement



EU RoHS Certificate of Compliance (PDF)



Multiple Part Product Compliance Statements
EU RoHS, REACH SVHC, & Low-Halogen



Multiple Part Industry Compliance Documents

*IPC 1752A Class C
 *IPC 1752A Class D
 *Molex Product Compliance Declaration
 *IEC-62474
 *chemSHERPA (xml)

View Molex Environmental Position Statements: [Click here](#)

Request Molex's CMRT from conflictminerals@molex.com

Part Detail

► General

► Physical

► Material Info

Application Tooling

[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

PRODUCTS+

[Product Categories](#)
[Product Index](#)
[Industries](#)

QUICK LINKS+

[Company Information](#)
[Contact Molex](#)
[Cross-Reference](#)
[Koch Industries](#)

RESOURCES+

[Supply Chain Transparency](#)
[Business Continuity](#)
[Compliance](#)
[ecocare](#)

STAY CONNECTED



[Investor Relations](#)

[Literature](#)

[Press Room / Press Releases](#)

[Sitemap](#)

[Terms & Conditions](#)

[Help](#)

[Jobs](#)

[Legal | Trademarks](#)

[Supplier Portal](#)

[Privacy Policy](#)

[Tradeshows](#)



Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2019