





DB UNLIMITED

Part Number:	DRAWN	1/20/2017
	CJ	
	CHECKED	1/20/2017
Description:	P.D	J.S
	APPROVED	1/20/2017
This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com		


Top View



Side View



Bottom View



Items	Specifications	Conditions				
Sound Pressure Level	93	dB (@ 10cm)				
Resonant Frequency	2,830	Hz				
Rated Voltage	3.6	V				
Voltage Range	3 ~ 4.5	V				
Coil Resistance	18 ± 5	Ω				
Max. Rated Current	100	mA				
Storage Temperature	-40 ~ +85	°C				
Operating Temperature	-20 ~ +70	°C				
Connection Method	Surface Pads					
Mount Type	Surface Mount					
Housing Material	LCP					
Weight	0.8	g				

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
	Released from Engineering	8/27/2014	J.S.
1	Updated to new template	1/20/2017	J.S.
2	Corrected voltage range and weight	5/18/2017	C.E.

NOTES			
1) All dimensions are in mm unless otherwise noted			
2) All tolerances are ± 0.2 mm unless otherwise noted			
3) All parts meet RoHS			
4) Subject to change or redrawn without notice			