

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BE-2RB

CATALOG LISTING

BE-2RB

PAGE 1 OF 1

RELEASE NO. PR-7892

REPLACES

DRAWING NUMBER

6

ISSUE

CHECK

REVISIONS

FORMTEK

FO-52848-A

DRAWN

WJM


18 MAY 79

CHECK

CEB

21 MAY 79

CHECK



NOTE
 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF $.139$ MAX DIA ON $1.000 \pm .002$ CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS

OPERATING FORCE ----- 14-22 OZ
 RELEASE FORCE ----- 10 OZ MIN
 DIFFERENTIAL TRAVEL - .0020-.0075
 OVERTRAVEL ----- .094 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
 S P D T

25A, 125, OR 250 VAC
 1HP 125 VAC, 2HP 250 VAC
 PILOT DUTY
 750 VA 125, 250 OR 277 VAC
 60/75°C (Cu)

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE $\pm$

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/04	
ONE PLACE	X,X	0.4/016	X X
TWO PLACES	X,X	0.15/006	X XX
THREE PLACES			X XXX
ANGLES			

DESIGN UNITS ☐ SI METRIC ☒ US CUSTOMARY

WEIGHT .004 LB

