




	1	2	3	4	5	6	7																																																																	
A								A																																																																
B								B																																																																
C								C																																																																
D	12.50 ±0.1 11.10 ±0.1 2-4.00 2-2.00 1.84 ±0.05 5.12 ±0.1 4-5.3 4.13 2.34 13.87 2-1.00 2-3.50 15.02 1.25 11.78 6.52 8-1.25 9-0.90 10.00 5.00 5-2.15 4-2.60 2-ø2.00 1.12 2.52 13.60 6.80 3.40 2.00 9 1 8 2 7 3 6 4 5							D																																																																
E	RECOMMENDED P.C.B LAYOUT TOLERANCES: ±0.05mm							E																																																																
F								F																																																																
G	RoHS compliant Unit: mm <table><tr><th>Scale</th><th>Free</th><th></th><th></th><th></th><th></th><th></th><th></th></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.X</td><td>±0.38</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.XX</td><td>±0.25</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.XXX</td><td>±0.13</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td>①</td><td>Drawn</td><td></td><td></td><td></td><td></td></tr><tr><td>Angle</td><td>±1.5°</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td></td><td></td></tr></table>							Scale	Free							TOLERANCE								X.X	±0.38							X.XX	±0.25							X.XXX	±0.13							DIM	TOL									①	Drawn					Angle	±1.5°	Id.	Modification	Date	Name			G
Scale	Free																																																																							
TOLERANCE																																																																								
X.X	±0.38																																																																							
X.XX	±0.25																																																																							
X.XXX	±0.13																																																																							
DIM	TOL																																																																							
		①	Drawn																																																																					
Angle	±1.5°	Id.	Modification	Date	Name																																																																			
H	1	2	3	4	5	6	7	H																																																																
<table><tr><th>Customer-No.</th><th>Date</th><th>Name</th><th>Drawing-No.</th><th>Replace</th><th>Sheet</th></tr><tr><td></td><td>05.01.2018</td><td>Winnie</td><td>ASS 7851 CO</td><td></td><td>rev00</td></tr><tr><td></td><td>05.01.2018</td><td>Winnie</td><td>AUSB3-AFN-HSR2</td><td></td><td></td></tr></table>							Customer-No.	Date	Name	Drawing-No.	Replace	Sheet		05.01.2018	Winnie	ASS 7851 CO		rev00		05.01.2018	Winnie	AUSB3-AFN-HSR2																																																		
Customer-No.	Date	Name	Drawing-No.	Replace	Sheet																																																																			
	05.01.2018	Winnie	ASS 7851 CO		rev00																																																																			
	05.01.2018	Winnie	AUSB3-AFN-HSR2																																																																					
ASSMANN components																																																																								
NOTES: Material: Insulator: Thermoplastic(UL94HB) (Pantone 300C) Color:Blue Contact: Copper Alloy Shell: Copper Alloy Contact Plating : Underplated:80u" Nickel Contact area:30u" Gold Solder tails area: 100u"-200u" matte tin Electrical : 1. Dielectrical withstanding rating: 100VAC /minute 2. Current rating: 1.8A(max) shall be applied to Vbus pin and its corresponding GND pin .0.25Amp (min) shall be applied to all the other contacts . 3. Contact resistance : 30mΩ(max)initial for VBUS and GND conactcs 50mΩ(max)initial for all other contacts Insulation Resistance : 100MΩ Min @250VDC Temperature Range:-20°C~85°C Mating cycles:5,000 insertions Packing : Tape&Reel																																																																								