

2.4W LMT2608 80.0:1 Transformer

FOR REFERENCE USE ONLY

DESCRIPTION

This document describes and specifies the electrical and mechanical characteristics of the SGE2668-1G high voltage transformer for CCFL inverter power supplies. SGE2668-1G is the RoHS compliant and Lead free transformer. For Reliability and Safety Specification, refer to SGE2606-4.


ELECTRICAL CHARACTERISTICS

Items	Inductance (@ 10KHz, 0.1V)			Items	DC. Resistance		
	Min	Nom	Max		Min	Nom	Max
L1-2, L2-3 (μH)	22	29	37	R _{DC} 1-2, R _{DC} 2-3 (mΩ)	100	118	128
L4-5 (mH)	300	433	547	R _{DC} 4-5 (Ω)	470	493	560
L _{LKG1-2, L_{LKG2-3}} (μH)	Inductance (@ 100KHz, 1V), with Short pin4-5			R1-2/R2-3	0.96	1	1.04
	6.2	6.7	7.4	Quality Factor Q ₁₋₃	30	50	
L _{LKG4-5} (mH)	NA	NA	NA	Quality Factor Q ₄₋₅	NA	NA	NA
Rating				Dielectric Voltage Withstand			
Note: Max output power varies depend on operating condition.				60Hz, Arc-detect enabled, 5 sec. min. 200μA max. leakage current			
Max Open Output Voltage	1500V _{RMS} , 3sec.			Secondary to Core	1500V _{RMS} min. (1min)		
Max Output Voltage	1000V _{RMS}			Primary to Core	750V _{RMS} min.		
Max Output Power	2.4W			Primary to Secondary	1000V _{RMS} min.		

WINDING SPECIFICATIONS

	Primary		Secondary
	Pin 1 - 2	Pin 2 - 3	Pin 4 - 5
Winding Sequence	1S - 2F	2S - 3F	5S - 4F
Wire Size & Type	0.18φ, Single Insulation, 180°C	0.18φ, Single Insulation, 180°C	0.03φ, Triple Insulation, 180°C
Number of Turns	13	13	1600
Winding Method	Bifilar		

PHYSICAL SPECIFICATIONS & WIRING DIAGRAM



Note : This transformer is design for single ended application. Pin 5 must to be connected to low voltage side or ground.

PART MARKING

SGE□□□□-□G XYZD A - SGE2668-1G: MSC PN,
PYMDD A: P: Plant Code, Y=Year, M:Month, DD:date A: Rev.#

PACKAGING SPEC AND ORDER INFORMATION

Packaging Order Information - SGE2668-1GTR (Tape and Reel)
TAPE & REEL : Refer to SGE2604-4 specification



Microsemi[®]

Specification Number
SGE2668-1G
Revision. A (051106)

2.4W LMT2608 80.0:1 Transformer

NOTES

PRODUCTION DATA – Information contained in this document is proprietary to Microsemi and is current as of publication date. This document may not be modified in any way without the express written consent of Microsemi. Product processing does not necessarily include testing of all parameters. Microsemi reserves the right to change the configuration and performance of the product and to discontinue product at any time.