




P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	REV. BY ECO-11-009578	10MAY2011	HC	WLS
	C2	REV. BY ECO 16-003728	11MAR2016	HC	WLS
	C3	REVISED PER ECN-23-197367	09FEB2023	WLS	DT

SUGESTED MATING TAB





- 1 MATERIAL: 1/2 HARD BRASS OR NICKEL PLATED STEEL.
- 2 NO BURRS PERMISSIBLE AT HOLE.
- 3 MUST BE FLAT WITHIN 0.076 MM OVER THIS LENGHT.
- 4 TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMPERATURE IS OVER 107°C.
- 5 HOLE MUST BE SYMMETRICAL ABOUT TAB CENTER WITHIN 0.076 MM.
- 6 TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.

LOGOTIPO E CODIGO DO PAÍS PRODUTOR
LOGO AND MANUFACTURING COUNTRY CODE.



1- WIRE RANGE 0,50 / 1,00 mm²
INSULATION DIA. RANGE Ø2,00 / 2,70 mm.

PARA LINGUETA ESPESSURA 0,8mm
FOR 0,8mm TAB THK.



OBSELETE	ESTANHADO/TINNED	LATÃO/BRASS	1380088-2
	NU/NONE	LATÃO/BRASS	1380088-1
	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.C.CANTERI CHK W.L.STEFANI APVD - 09AUG00 09AUG00 09AUG00	TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME POSITIVE LOCK MKIII, L.I.F. .250 SERIES RECEPT.		
MATERIAL SEE TABLE		FINISH SEE TABLE		SIZE A2	CAGE CODE 00779	DRAWING NO C-1380088
				RESTRICTED TO -		
				SCALE 10:1	SHEET 1	REV C3