



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: DBMC (.8% in M-45195-1) Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts




TE Part # 172198-2
ECONOSEAL-J CONN PLUG 2P
BLACK



TE Part # 172199-1
ECONOSEAL-J CONN CAP 2P
NATURA

Customers Also Bought



TE Part #34319
SPLICE,SOLIS PARA 6



TE Part #CAT-AM7017-H342
AMP COMMON TERMINATION
HEADERS



TE Part #2040805-1
1mm WIRE TO BOARD INTERNAL
REC ASSY R/A




TE Part #170292-1
2 DIA PIN LANCE LESS L.P.




TE Part #172779-1
MIC MARK-2 TAB CONTACT




TE Part #2237023-1
40P 025 CAP ASSY



TE Part #172198-1
ECONOSEAL-J CONN PLUG 2P



TE Part #172203-1
ECONOSEAL-J CONN RUBBER 3P



TE Part #917532-1
Q40 MLC T.F. CAP HSG 14P NATU

Documents

Product Drawings
ECONOSEAL-J CONN RUBBER 2P

English

CAD Files
3D PDF
3D



Customer View Model
[ENG_CVM_CVM_172200-1_B.2d_dxf.zip](#)
English
Customer View Model
[ENG_CVM_CVM_172200-1_B.3d_igs.zip](#)
English
Customer View Model
[ENG_CVM_CVM_172200-1_B.3d_stp.zip](#)
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
[Product Specification](#)
Japanese

Instruction Sheets
[AMP ECONOSEAL* SERIES "J" CONNECTOR](#)
English
[AMP ECONOSEAL* SERIES "J" CONNECTOR](#)
English
[AMP ECONOSEAL* SERIES "J" CONNECTOR](#)
Japanese
[AMP ECONOSEAL* SERIES "J" CONNECTOR](#)
Japanese