



Pushing Performance
Since 1945

Han PP PFT plastic rect. crimp power



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 231 0331
Specification	Han PP PFT plastic rect. crimp power
HARTING eCatalogue	https://harting.com/09352310331

Identification

Category	Connectors
Series	Han® PushPull (V14)
Identification	Power
Element	Panel feed trough set
Features	Intuitive locking mechanism

Version

Termination method	Crimp termination
Shielding	Unshielded
Number of contacts	5
Locking type	PushPull
Pack contents	incl. bulkhead mounted housing and male insert Without contacts

Technical characteristics

Conductor cross-section	0.25 ... 2.5 mm²
Conductor cross-section [AWG]	AWG 22 ... AWG 12
Rated current	16 A
Rated voltage	690 V
Rated impulse voltage	8 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Limiting temperature	-40 ... +70 °C



Pushing Performance
Since 1945

Technical characteristics

Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67
Vibration resistance	5-150 Hz, 5 g, 0.35 mm, 2h/axis
Shock resistance	5 g / 30 ms, 3 shocks / axis and direction

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	Grey
Surface (contacts)	Silver plated
Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61076-3-118 EN 45545-2
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	10.22 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140054165
eCl@ss	27440114 Rectangular connector (for field assembly)



Pushing Performance
Since 1945

Commercial data

ETIM	EC002636
UNSPSC 24.0	39121408

Mating face

