



HONEYWELL PART NUMBER
91SX41
PRODUCT CODE VDQ9110

REV	DOCUMENT	CHANGED BY	CHECK
5	0038450	PK 03JUN08	ASD



NOTES
1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 DIA ON .188±.0002 CENTERS
2 - TERMINALS ARE PLATED FOR SOLDERING

RELEASE NO.	PR-17692
REPLACES	

CHARACTERISTICS		ELECTRICAL DATA				DESIGN UNITS: INCH		DRAWN	SPK	04MAR08	Honeywell				
OPERATING FORCE ----- 5 OZ MAX		CONTACT ARRANGEMENT S P D T				TOLERANCES UNLESS NOTED:		CHECK	RJ	04MAR08					
RELEASE FORCE----- 1 OZ MIN			28 VOLTS DC RATING		115 VOLTS AC, 60 CPS		NO PLACE X ±	0.030 0.015 0.005	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC			
DIFFERENTIAL TRAVEL--- .005 MAX			SEA LEVEL		SEA LEVEL		ONE PLACE .X ±								
OVERTRAVEL----- .004 MIN		INDUCTIVE	4 AMP	2.5 AMP	7 AMP		TWO PLACE .XX ±								
		RESISTIVE	7 AMP	4 AMP	7 AMP		THREE PLACE .XXX ±								
		LAMP	2.5 AMP	2.5 AMP	2 AMP		FOUR PLACE .XXXX ±								
		APPROVALS					ANGLES ±	INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV
							THIRD ANGLE PROJECTION			B	I	91SX41		5	
										RASTER			SCALE	-	WEIGHT:.003 LB MAX