






|                       |                                                                                              |
|-----------------------|----------------------------------------------------------------------------------------------|
| Order Code            | TCK-070                                                                                      |
| Inductance            | 10 µH ±20% (at 1 kHz / 250 mV)                                                               |
| Impedance (DCR)       | 40 mΩ max.                                                                                   |
| Rated Current         | 2.6 A max.                                                                                   |
| Operating Temperature | -40°C to +125°C                                                                              |
| RoHS Exemptions       | No Exemptions                                                                                |
| Overview Link         | <a href="http://www.tracopower.com/overview/tck-070">www.tracopower.com/overview/tck-070</a> |



Impedance Curve



Outline Dimensions



| Dimensions [mm] |          |
|-----------------|----------|
| A               | 7.0 ±0.5 |
| B               | 7.8 ±0.5 |
| C               | 5.0 ±0.7 |
| D               | 2.1 typ. |
| E               | 7.5      |
| F               | 3        |
| G               | 2        |

All specifications valid at +25°C, unless otherwise stated.