

Part Number : 1000570026

Series Number : 100057

Product Category : Specialty Wire and Cable

Product Description : Temp-Flex High-Performance Flat-Ribbon Cable, 60 Circuits, 0.64mm Pitch, 30 AWG, Silver Plated Copper, UL 20726, 7/38 Stranded Extruded FEP, Natural with Blue Polarity Stripe

Status : Active

Engineering Number : F3007S-60-025-85

Documents & Resources

Drawings

Drawing 1000570026_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Specialty Wire and Cable
Series	100057
Description	Temp-Flex High-Performance Flat-Ribbon Cable, 60 Circuits, 0.64mm Pitch, 30 AWG, Silver Plated Copper, UL 20726, 7/38 Stranded Extruded FEP, Natural with Blue Polarity Stripe
Product Family	Temp-Flex Flat Ribbon Cable Solutions
Product Name	Temp-Flex
UPC	887191902715

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	150V AC

Physical

Cable Length	100 ft/spool, 10 ft min length
Circuits (Loaded)	60
Color - Cable Jacket	Natural w/Blue Polarity Stripe
Insulation	FEP
Material - Outer Jacket	FEP
Material - Plating Mating	Silver
Packaging Type	Spool
Pitch - Mating Interface	0.64mm
Temperature Range - Operating	-55° to +150°C
Wire/Cable Type	7/38 Stranded, High-Performance Flat-Ribbon, UL 20726
Wire Size (AWG)	30

Use with Part(s)

Description	Part Number
Use With	Molex Picoflex

This document was generated on Jul 21, 2024