
© 2023 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECN-24-269130	12JUN2024	DK	LC





1 MATERIAL: SEE TABLE


2 RECOMMENDED MATING PART: X-2465651-X


3 PACKAGING: ON REEL

4 REFERENCE CRIMP INFORMATION:
WIRE RANGE: 16-22AWG COPPER STRANDED
INSULATION RANGE:2.0-3.3mm,
2.0-2.5mm (WITH TPA)









TIN PRE-PLATED	COPPER ALLOY, 0.25THICK	2465656-1
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±0.2
2 PLC ±0.2
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL: SEE TABLE

FINISH: SEE TABLE

DWN: MADHUVARSHINI 11SEP2023
CHK: CHEN OTTO 11SEP2023
APVD: DANIEL ZHANG 11SEP2023
PRODUCT SPEC: 108-160978
APPLICATION SPEC: 114-160619
WEIGHT: -

TE Connectivity

NAME: REC TERMINAL 16-22AWG, QP 6.5

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-2465656	-

CUSTOMER DRAWING | SCALE 10:1 | SHEET 1 OF 1 | REV A

4805 (3/13)

Downloaded from Arrow.com.