
DATA SHEET

MINI141 K-18, 2.9mm (male), 2.9mm (male), 50 Ohm, 40 GHz, 18 in, 457.2 mm

MINI141 K-18

Properties

- Applicable up to 40 GHz
- Part of the "bend-to-the-end" MINIBEND product family
- Direct replacement for 141 size Semi-Rigid cables
- Compliant to MIL-DTL-17 (cable) and MIL-PRF-39012 (connectors)
- Solderless cable junction
- Low loss PTFE dielectric



Product configuration	
Configuration type	One pair of assemblies
Type of cable	MINI141 (32022E)
Type description connector A	29094KCR-32-22
Series connector A	PC 2.9, straight - plug
Type description connector B	29094KCR-32-22
Series connector B	PC 2.9, straight - plug
Length	457.2 mm
Length	18 inch
Length type	REF to REF

Electrical data	
Impedance	50 Ω
Max. operating frequency	40 GHz
VSWR max	1.45
Propagation velocity	76 %

Electrical Data (frequency related)			
Frequency range	**Return loss**	**VSWR max**	**Insertion loss**
0 GHz ... 2 GHz	23.12 dB	1.15	0.36 dB
2 GHz ... 18 GHz	16.53 dB	1.35	1.07 dB
18 GHz ... 26.5 GHz	15.56 dB	1.4	1.31 dB
26.5 GHz ... 40 GHz	14.71 dB	1.45	1.76 dB

Downloaded from Arrow.com.

MINI141 K-18, 2.9mm (male), 2.9mm (male), 50 Ohm, 40 GHz, 18 in, 457.2 mm

MINI141 K-18

Mechanical data	
Weight	0.017 kg
Cable diameter	3.61 mm
Static bending radius	8.38 mm
Dynamic bending radius	25.15 mm

Environmental data	
Operation temperature	-55 °C ... 125 °C

Ordering information	
Item number	Item description
80360540	MINI141 K-18

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P59680 / Date of publication: 13.02.2026 / uncontrolled copy

Downloaded from Arrow.com.