



## Technical Data

27.12.2021

Shrinkable markers "Continuous Tube", thermal transfer  
TULT – 3:1 Military and Electronics

**TULT18-6WH**

**Article Number 553-41851**



Material:

Polyolefin, cross-linked (PO-X)

Colour:

White (WH)

Supplied Ø D min.:

18.0 mm

Recov. Ø d max.:

6.0 mm

Wall (WT):

0.90 mm

Shrink Ratio:

3:1

Min. Shrink Temperature - °C:

+90 °C

Test Method

Flammability:

UL 224 VW-1

Operating Temperature - °C:

-55 °C to +135 °C

Dielectric Strength:

37 kV/mm

ASTM D876

Insulation Class:

B (VDE 0530)

Longitudinal Change After Shrinkage:

-15% max.

We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved



## Technical Data

27.12.2021

Shrinkable markers "Continuous Tube", thermal transfer  
TULT – 3:1 Military and Electronics

Print Method:

Thermal transfer printing

Application Tool:

H6100, TT431, TT4030, TrakMark DS



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved