




**Part Number :** [757101008](#)  
**Product Description :** GbX I-Trac Right-Angle Daughtercard Module, 1.85mm by 3.70mm Pitch, Unguided, 11 Rows, 8 Columns, 176 Circuits  
**Series Number :** 75710  
**Status :** Active  
**Product Category :** Backplane Connectors



## Documents & Resources


**Drawings**  
[757101008\\_sd.pdf](#)  
[PK-70873-609-001.pdf](#)

**3D Models and Design Files**  
[757101008\\_stp.zip](#)

**Specifications**  
[PS-45499-002-001.pdf](#)  
[PS-75710-999-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements  
- Eu RoHS  
- REACH SVHC  
- Low-Halogen

Multiple Part Industry Compliance Documents  
- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Backplane Connectors
Series	75710
Description	GbX I-Trac Right-Angle Daughtercard Module, 1.85mm by 3.70mm Pitch, Unguided, 11 Rows, 8 Columns, 176 Circuits
Application	Coplanar, Daughtercard
Component Type	PCB Receptacle
Product Name	GbX I-Trac
UPC	822350838078

#### Agency

UL	E29179
----	--------

#### Electrical

Current - Maximum per Contact	1.0A
Data Rate	12.0 Gbps
Shield Type	N/A
Shielded	No
Voltage - Maximum	120V AC (RMS)/DC

#### Physical

Circuits (Loaded)	176
Circuits (maximum)	176
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No

Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	21.828/g
Number of Columns	8
Number of Pairs	Open Pin Field
Number of Rows	11
Orientation	Right Angle
Packaging Type	Tray
PC Tail Length	2.00mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	1.85mm, 3.70mm
Pitch - Termination Interface	1.00mm, 2.70mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to PCB	No
Stackable	Yes
Temperature Range - Operating	-55° to +80°C
Termination Interface Style	Through Hole - Compliant Pin

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
GbX I-Trac Vertical Header Modules	<u>75705</u>

### Use with Part(s)

Description	Part Number
-------------	-------------

GbX I-Trac Right-Angle Headers	<u>78234</u>
Wide Guide Modules and Pins	<u>76153</u>

This document was generated on Mar 03, 2025