


MLCC Gold Termination – AU Series

General Specifications



KYOCERA AVX will support those customers for commercial and military Multilayer Ceramic Capacitors with a termination consisting of Gold. This termination is indicated by the use of a "7" or "G" in the 12th position of the KYOCERA AVX Catalog Part Number. This fulfills KYOCERA AVX's commitment to providing a full range of products to our customers. Please contact the factory if you require additional information on our MLCC Gold Termination.

PART NUMBER

AU03	Y	G	104	K	A	7	2	A
Size	Voltage	Dielectric	Capacitance Code (In pF)	Capacitance Tolerance	Failure Rate	Terminations	Packaging	Special Code
AU02 - 0402 AU03 - 0603 AU05 - 0805 AU06 - 1206 AU10 - 1210 AU12 - 1812 AU13 - 1825 AU14 - 2225 AU16 - 0306 AU17 - 0508 AU18 - 0612	6.3V = 6 10V = Z 16V = Y 25V = 3 35V = D 50V = 5 100V = 1 200V = 2 500V = 7	C0G (NP0) = A X7R = C X5R = D	2 Sig. Digits + Number of Zeros	B = ±10 pF (<10pF) C = ±.25 pF (<10pF) D = ±.50 pF (<10pF) F = ±1% (≥ 10 pF) G = ±2% (≥ 10 pF) J = ±5% K = ±10% M = ±20%	A = Not Applicable	G* = 1.9 μ" to 7.87 μ" 7 = 100 μ" minimum	2 = 7" Reel 4 = 13" Reel U = 4mm TR (01005) Contact Factory For Multiples*	A = Std. Product

* Contact factory for availability.

MLCC Gold Termination – AU Series


Capacitance Range (NP0 Dielectric)



PREFERRED SIZES ARE SHADED

SIZE	AU02				AU03				AU05					AU06					
Soldering	Reflow/Epoxy/ Wire Bond*				Reflow/Epoxy/ Wire Bond*				Reflow/Epoxy/ Wire Bond*					Reflow/Epoxy/ Wire Bond*					
Packaging	All Paper				All Paper				Paper/Embossed					Paper/Embossed					
(L) Length	mm (in.)	1.00 ± 0.10 (0.040 ± 0.004)			1.60 ± 0.15 (0.063 ± 0.006)				2.01 ± 0.20 (0.079 ± 0.008)					3.20 ± 0.20 (0.126 ± 0.008)					
(W) Width	mm (in.)	0.50 ± 0.10 (0.020 ± 0.004)			0.81 ± 0.15 (0.032 ± 0.006)				1.25 ± 0.20 (0.049 ± 0.008)					1.60 ± 0.20 (0.063 ± 0.008)					
(t) Terminal	mm (in.)	0.25 ± 0.15 (0.010 ± 0.006)			0.35 ± 0.15 (0.014 ± 0.006)				0.50 ± 0.25 (0.020 ± 0.010)					0.50 ± 0.25 (0.020 ± 0.010)					
	WVDC	16	25	50	16	25	50	100	16	25	50	100	200	16	25	50	100	200	500
Cap (pF)	0.5	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	1.0	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	1.2	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	1.5	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	1.8	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	2.2	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	2.7	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
		3.3	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J
3.9		C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
4.7		C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
		5.6	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J
	6.8	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	8.2	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
		10	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J
12		C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
15		C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
		18	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J
	22	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	27	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
		33	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J
39		C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
47		C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
		56	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J
	68	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	82	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
		100	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J
120		C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
150		C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
		180	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J
	220	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	M
	270	C	C	C	G	G	G	G	J	J	J	J	M	J	J	J	J	J	M
		330	C	C	C	G	G	G	G	J	J	J	J	M	J	J	J	J	J
390		C	C	C	G	G	G		J	J	J	J	M	J	J	J	J	J	M
470		C	C	C	G	G	G		J	J	J	J	M	J	J	J	J	J	M
		560				G	G	G		J	J	J	J	M	J	J	J	J	J
	680				G	G	G		J	J	J	J	M	J	J	J	J	J	P
	820				G	G	G		J	J	J	J	M	J	J	J	J	M	
		1000				G	G	G		J	J	J	J	M	J	J	J	J	Q
1200									J	J	J	J		J	J	J	J	Q	
1500									J	J	J	J		J	J	J	M	Q	
		1800								J	J	J			J	J	M	M	
	2200								J	J	J	N		J	J	M	P		
	2700								J	J	J	N		J	J	M	P		
		3300								J	J				J	J	M	P	
3900									J	J				J	J	M	P		
4700									J	J				J	J	M	P		
		5600													J	J	M		
	6800													M	M				
	8200													M	M				
		0.010													M	M			
0.012																			
0.015																			
		0.018																	
	0.022																		
	0.027																		
		0.033																	
0.039																			
0.047																			
		0.068																	
	0.082																		
	0.1																		
	WVDC	16	25	50	16	25	50	100	16	25	50	100	200	16	25	50	100	200	500
SIZE	AU02			AU03				AU05					AU06						

* Contact Factory



Letter	A	C	E	G	J	K	M	N	P	Q	X	Y	Z
Max. Thickness	0.33 (0.013)	0.56 (0.022)	0.71 (0.028)	0.90 (0.035)	0.94 (0.037)	1.02 (0.040)	1.27 (0.050)	1.40 (0.055)	1.52 (0.060)	1.78 (0.070)	2.29 (0.090)	2.54 (0.100)	2.79 (0.110)
	PAPER					EMBOSSED							

MLCC Gold Termination – AU Series

Capacitance Range (NP0 Dielectric)

PREFERRED SIZES ARE SHADED

SIZE		AU10					AU12					AU13			AU14		
Soldering		Reflow/Epoxy/ Wire Bond*					Reflow/Epoxy/ Wire Bond*					Reflow/Epoxy/ Wire Bond*			Reflow/Epoxy/ Wire Bond*		
Packaging		Paper/Embossed					All Embossed					All Embossed			All Embossed		
(L) Length	mm	3.20 ± 0.20					4.50 ± 0.30					4.50 ± 0.30			5.72 ± 0.25		
	(in.)	(0.126 ± 0.008)					(0.177 ± 0.012)					(0.177 ± 0.012)			(0.225 ± 0.010)		
(W) Width	mm	2.50 ± 0.20					3.20 ± 0.20					6.40 ± 0.40			6.35 ± 0.25		
	(in.)	(0.098 ± 0.008)					(0.126 ± 0.008)					(0.252 ± 0.016)			(0.250 ± 0.010)		
(t) Terminal	mm	0.50 ± 0.25					0.61 ± 0.36					0.61 ± 0.36			0.64 ± 0.39		
	(in.)	(0.020 ± 0.010)					(0.024 ± 0.014)					(0.024 ± 0.014)			(0.025 ± 0.015)		
	WVDC	25	50	100	200	500	25	50	100	200	500	50	100	200	50	100	200
Cap (pF)	0.5																
	1.0																
	1.2																
	1.5																
	1.8																
	2.2																
	2.7																
	3.3																
	3.9																
	4.7																
	5.6																
	6.8																
	8.2																
	10					J											
	12					J											
	15					J											
	18					J											
	22					J											
	27					J											
	33					J											
	39					J											
	47					J											
	56					J											
	68					J											
	82					J											
	100					J											
	120					J											
	150					J											
	180					J											
	220					J											
	270					J											
	330					J											
	390					M											
	470					M											
	560	J	J	J	J	M											
	680	J	J	J	J	M											
	820	J	J	J	J	M											
	1000	J	J	J	J	M	K	K	K	K	M	M	M	M	M	M	P
	1200	J	J	J	M	M	K	K	K	K	M	M	M	M	M	M	P
	1500	J	J	J	M	M	K	K	K	K	M	M	M	M	M	M	P
	1800	J	J	J	M	M	K	K	K	K	M	M	M	M	M	M	P
	2200	J	J	J	Q		K	K	K	K	P	M	M	M	M	M	P
	2700	J	J	J	Q		K	K	K	P	Q	M	M	M	M	M	P
	3300	J	J	J			K	K	K	P	Q	M	M	M	M	M	P
	3900	J	J	M			K	K	K	P	Q	M	M	M	M	M	P
	4700	J	J	M			K	K	K	P	Q	M	M	M	M	M	P
	5600	J	J				K	K	M	P	X	M	M	M	M	M	P
	6800	J	J				K	K	M	X		M	M	M	M	M	P
	8200	J	J				K	K	M			M	M	M	M	M	P
	0.010	J	J				K	M	M			M	M		M	M	P
	0.012	J	J				K	M				M	M		M	M	P
	0.015						M	M				M	M		M	M	Y
	0.018						M	M				P	M		M	M	Y
	0.022						M	M				P			M	Y	Y
	0.027						M	M				P			P	Y	Y
	0.033						M	M				P			P		
	0.039						M	M				P			P		
	0.047						M	M				P			P		
	0.068						M	M							P		
	0.082						M	M							Q		
	0.1														Q		
	WVDC	25	50	100	200	500	25	50	100	200	500	50	100	200	50	100	200
SIZE		AU10					AU12					AU13			AU14		

* Contact Factory

Letter	A	C	E	G	J	K	M	N	P	Q	X	Y	Z
Max. Thickness	0.33 (0.013)	0.56 (0.022)	0.71 (0.028)	0.90 (0.035)	0.94 (0.037)	1.02 (0.040)	1.27 (0.050)	1.40 (0.055)	1.52 (0.060)	1.78 (0.070)	2.29 (0.090)	2.54 (0.100)	2.79 (0.110)
	PAPER					EMBOSSED							

MLCC Gold Termination – AU Series

Capacitance Range (X7R Dielectric)



PREFERRED SIZES ARE SHADED

SIZE		AU02				AU03								AU05								AU06							
Soldering		Reflow/Epoxy/ Wire Bond*				Reflow/Epoxy/ Wire Bond*								Reflow/Epoxy/ Wire Bond*								Reflow/Epoxy/ Wire Bond*							
Packaging		All Paper				All Paper								Paper/Embossed								Paper/Embossed							
(L) Length	mm	1.00 ± 0.10				1.60 ± 0.15								2.01 ± 0.20								3.20 ± 0.20							
	(in.)	(0.040 ± 0.004)				(0.063 ± 0.006)								(0.079 ± 0.008)								(0.126 ± 0.008)							
W) Width	mm	0.50 ± 0.10				0.81 ± 0.15								1.25 ± 0.20								1.60 ± 0.20							
	(in.)	(0.020 ± 0.004)				(0.032 ± 0.006)								(0.049 ± 0.008)								(0.063 ± 0.008)							
(t) Terminal	mm	0.25 ± 0.15				0.35 ± 0.15								0.50 ± 0.25								0.50 ± 0.25							
	(in.)	(0.010 ± 0.006)				(0.014 ± 0.006)								(0.020 ± 0.010)								(0.020 ± 0.010)							
WVDC		10	16	25	50	63	10	16	25	50	100	200	63	10	16	25	50	100	200	63	10	16	25	50	100	200	500		
Cap (pF)	100																												
	150																												
	220				C				G																				
	330				C					G	G	G		J	J	J	J	J	J							K			
	470				C					G	G	G		J	J	J	J	J	J							K			
	680				C					G	G	G		J	J	J	J	J	J							K			
	1000				C					G	G	G		J	J	J	J	J	J							K			
	1500				C					G	G	G		J	J	J	J	J	J		J	J	J	J	J	M			
	2200				C					G	G	G		J	J	J	J	J	J		J	J	J	J	J	M			
	3300			C	C					G	G	G		J	J	J	J	J	J		J	J	J	J	J	J	M		
	4700			C	C					G	G	G		J	J	J	J	J	J		J	J	J	J	J	M			
	6800		C	C						G	G	G		J	J	J	J	J	J		J	J	J	J	J	P			
Cap (μF)	0.010		C					G		G	G			J	J	J	J	J	J		J	J	J	J	J	J	P		
	0.015		C						G	G	G			J	J	J	J	J	J		J	J	J	J	M				
	0.022	C	C						G	G	G			J	J	J	J	J	N		J	J	J	J	M				
	0.033	C							G	G	G			J	J	J	J	N			J	J	J	J	M				
	0.047								G	G	G			J	J	J	J	N			J	J	J	J	M				
0.068								G	G	G			J	J	J	J	N			J	J	J	J	P					
	0.10						G	G	G	G				J	J	J	J				J	J	J	J	M	P			
	0.15					G	G						J	J	J	N	N				J	J	J	J	Q				
	0.22					G	G						J	J	N	N	N				J	J	J	J	Q				
	0.33													N	N	N	N	N			J	J	M	P	Q				
	0.47													N	N	N	N				M	M	M	Q	Q				
	0.68													N	N	N					M	M	Q	Q	Q				
	1.0													N	N	N					M	M		Q	Q				
	1.5																				P	Q	Q						
	2.2															P*					Q	Q	Q						
	3.3																												
	4.7													P*							Q	Q							
	10																				Q*								
	22																			Q*									
	47																												
	100																												
WVDC		10	16	25	50	63	10	16	25	50	100	200	63	10	16	25	50	100	200	63	10	16	25	50	100	200	500		
SIZE		AU02				AU03								AU05								AU06							

* Contact Factory


Letter	A	C	E	G	J	K	M	N	P	Q	X	Y	Z
Max. Thickness	0.33 (0.013)	0.56 (0.022)	0.71 (0.028)	0.90 (0.035)	0.94 (0.037)	1.02 (0.040)	1.27 (0.050)	1.40 (0.055)	1.52 (0.060)	1.78 (0.070)	2.29 (0.090)	2.54 (0.100)	2.79 (0.110)
	PAPER					EMBOSSED							

MLCC Gold Termination – AU Series

Capacitance Range (X7R Dielectric)

PREFERRED SIZES ARE SHADED

SIZE		AU10							AU12				AU13		AU14	
Soldering		Reflow/Epoxy/ Wire Bond*							Reflow/Epoxy/ Wire Bond*				Reflow/Epoxy/ Wire Bond*		Reflow/Epoxy/ Wire Bond*	
Packaging		Paper/EmbossedU							All Embossed				All Embossed		All Embossed	
(L) Length	mm	3.20 ± 0.20							4.50 ± 0.30				4.50 ± 0.30		5.72 ± 0.25	
	(in.)	(0.126 ± 0.008)							(0.177 ± 0.012)				(0.177 ± 0.012)		(0.225 ± 0.010)	
W) Width	mm	2.50 ± 0.20							3.20 ± 0.20				6.40 ± 0.40		6.35 ± 0.25	
	(in.)	(0.098 ± 0.008)							(0.126 ± 0.008)				(0.252 ± 0.016)		(0.250 ± 0.010)	
(t) Terminal	mm	0.50 ± 0.25							0.61 ± 0.36				0.61 ± 0.36		0.64 ± 0.39	
	(in.)	(0.020 ± 0.010)							(0.024 ± 0.014)				(0.024 ± 0.014)		(0.025 ± 0.015)	
WVDC		10	16	25	50	100	200	500	50	100	200	500	50	100	50	100
Cap (pF)	100															
	150															
	220															
	330															
	470															
	680															
	1000															
	1500	J	J	J	J	J	J	M								
	2200	J	J	J	J	J	J	M								
	3300	J	J	J	J	J	J	M								
	4700	J	J	J	J	J	J	M								
	6800	J	J	J	J	J	J	M								
Cap (μF)	0.010	J	J	J	J	J	J	M	K	K	K	K	M	M	M	P
	0.015	J	J	J	J	J	J	P	K	K	K	P	M	M	M	P
	0.022	J	J	J	J	J	J	Q	K	K	K	P	M	M	M	P
	0.033	J	J	J	J	J	J	Q	K	K	K	X	M	M	M	P
	0.047	J	J	J	J	J	J		K	K	K	Z	M	M	M	P
	0.068	J	J	J	J	J	M		K	K	K	Z	M	M	M	P
	0.10	J	J	J	J	J	M		K	K	K	Z	M	M	M	P
	0.15	J	J	J	J	M	Z		K	K	P		M	M	M	P
	0.22	J	J	J	J	P	Z		K	K	P		M	M	M	P
	0.33	J	J	J	J	Q			K	M	X		M	M	M	P
	0.47	M	M	M	M	Q			K	P			M	M	M	P
	0.68	M	M	P	X	X			M	Q			M	P	M	P
	1.0	N	N		X	Z			M	X			M	P	M	P
	1.5	N	N	Z	Z	Z			Z	Z			M		M	X
	2.2	X	X	Z	Z	Z			Z	Z					M	
	3.3	X	X	Z	Z				Z							
	4.7	X	X	Z	Z				Z							
	10	Z	Z	Z												
	22															
	47															
	100															
WVDC		10	16	25	50	100	200	500	50	100	200	500	50	100	50	100
SIZE		AU10							AU12				AU13		AU14	



* Contact Factory

Letter	A	C	E	G	J	K	M	N	P	Q	X	Y	Z
Max. Thickness	0.33 (0.013)	0.56 (0.022)	0.71 (0.028)	0.90 (0.035)	0.94 (0.037)	1.02 (0.040)	1.27 (0.050)	1.40 (0.055)	1.52 (0.060)	1.78 (0.070)	2.29 (0.090)	2.54 (0.100)	2.79 (0.110)
	PAPER					EMBOSSED							

MLCC Gold Termination – AU Series

Capacitance Range (X5R Dielectric)



PREFERRED SIZES ARE SHADED

SIZE	AU02						AU03						AU05						AU06						AU10						AU12					
Soldering	Reflow/Epoxy Wire Bond*						Reflow/Epoxy Wire Bond*						Reflow/Epoxy Wire Bond*						Reflow/Epoxy Wire Bond*						Reflow/Epoxy Wire Bond*						Reflow/Epoxy Wire Bond*					
Packaging	All Paper						All Paper						Paper/Embossed						Paper/Embossed						Paper/Embossed						All Embossed					
(L) Length	mm	1.00 ± 0.10 (0.040 ± 0.004)					1.60 ± 0.15 (0.063 ± 0.006)						2.01 ± 0.20 (0.079 ± 0.008)						3.20 ± 0.20 (0.126 ± 0.008)						3.20 ± 0.20 (0.126 ± 0.008)						4.50 ± 0.30 (0.177 ± 0.012)					
(W) Width	mm	0.50 ± 0.10 (0.020 ± 0.004)					0.81 ± 0.15 (0.032 ± 0.006)						1.25 ± 0.20 (0.049 ± 0.008)						1.60 ± 0.20 (0.063 ± 0.008)						2.50 ± 0.20 (0.098 ± 0.008)						3.20 ± 0.20 (0.126 ± 0.008)					
(t) Terminal	mm	0.25 ± 0.15 (0.010 ± 0.006)					0.35 ± 0.15 (0.014 ± 0.006)						0.50 ± 0.25 (0.020 ± 0.010)						0.50 ± 0.25 (0.020 ± 0.010)						0.50 ± 0.25 (0.020 ± 0.010)						0.61 ± 0.36 (0.024 ± 0.014)					
WVDC	4	6.3	10	16	25	50	4	6.3	10	16	25	35	50	6.3	10	16	25	35	50	6.3	10	16	25	35	50	4	6.3	10	16	25	35	50	6.3	10	25	50
Cap (pF)	100																																			
	150																																			
	220																																			
	330					C																														
	470				C																															
	680				C																															
	1000				C																															
	1500				C																															
	2200				C																															
	3300				C																															
	4700				C								G																							
	6800				C								G																							
Cap (μF)	0.010				C								G																							
	0.015				C								G																							
	0.022				C								G																							
	0.033				C								G																							
	0.047				C								G																							
	0.068				C								G																							
	0.10		C		C								G																							
	0.15												G																							
	0.22		C*										G																							
	0.33												G																							
	0.47		C*										G																							
	0.68												G																							
	1.0												G																							
	1.5												G																							
	2.2		C*										G*																							
	3.3												J*																							
	4.7												J*																							
	10												J*																							
	22												K*																							
	47																																			
	100																																			
WVDC	4	6.3	10	16	25	50	4	6.3	10	16	25	35	50	6.3	10	16	25	35	50	6.3	10	16	25	35	50	4	6.3	10	16	25	35	50	6.3	10	25	50
SIZE	AU02						AU03						AU05						AU06						AU10						AU12					

* Contact Factory

Letter	A	C	E	G	J	K	M	N	P	Q	X	Y	Z
Max. Thickness	0.33 (0.013)	0.56 (0.022)	0.71 (0.028)	0.90 (0.035)	0.94 (0.037)	1.02 (0.040)	1.27 (0.050)	1.40 (0.055)	1.52 (0.060)	1.78 (0.070)	2.29 (0.090)	2.54 (0.100)	2.79 (0.110)
	PAPER					EMBOSSED							

= *Optional Specifications – Contact Factory

NOTE: Contact factory for non-specified capacitance values

MLCC Gold Termination – AU Series

AU16/AU17/AU18

SIZE		AU16 (0306)					AU17 (0508)					AU18 (0612)				
Packaging		Embossed					Embossed					Embossed				
Length	mm	0.81 ± 0.15					1.27 ± 0.25					1.60 ± 0.25				
	(in.)	(0.032 ± 0.006)					(0.050 ± 0.010)					(0.063 ± 0.010)				
Width	mm	1.60 ± 0.15					2.00 ± 0.25					3.20 ± 0.25				
	(in.)	(0.063 ± 0.006)					(0.080 ± 0.010)					(0.126 ± 0.010)				
Cap Code	WVDC	4	6.3	10	16	25	6.3	10	16	25	50	6.3	10	16	25	50
102	Cap .001		A	A	A	A	S	S	S	S	V	S	S	S	S	V
222	(μF) .0022		A	A	A	A	S	S	S	S	V	S	S	S	S	V
332	0.0033		A	A	A	A	S	S	S	S	V	S	S	S	S	V
472	0.0047		A	A	A	A	S	S	S	S	V	S	S	S	S	V
682	0.0068		A	A	A	A	S	S	S	S	V	S	S	S	S	V
103	0.01		A	A	A	A	S	S	S	S	V	S	S	S	S	V
153	0.015		A	A	A	A	S	S	S	S	V	S	S	S	S	W
223	0.022		A	A	A	A	S	S	S	S	V	S	S	S	S	W
333	0.033		A	A	A		S	S	S	V	V	S	S	S	S	W
473	0.047		A	A	A		S	S	S	V	A	S	S	S	S	W
683	0.068		A	A	A		S	S	S	A	A	S	S	S	V	W
104	0.1		A	A			S	S	V	A	A	S	S	S	V	W
154	0.15		A	A			S	S	V			S	S	S	W	W
224	0.22		A	A			S	S	A			S	S	V	W	
334	0.33						V	V	A			S	S	V		
474	0.47						V	V				S	S	V		
684	0.68						A	A				V	V	W		
105	1		A				A	A				V	V	A		
155	1.5											W	W			
225	2.2											A	A			
335	3.3											A				
475	4.7															
685	6.8															
106	10															

Solid = X7R

= X5R


= X7S

mm (in.)	
AU16 (0306)	
Code	Thickness
A	0.56 (0.022)

mm (in.)	
AU16 (0508)	
Code	Thickness
S	0.56 (0.022)
V	0.76 (0.030)
A	1.02 (0.040)

mm (in.)	
AU16 (0612)	
Code	Thickness
S	0.56 (0.022)
V	0.76 (0.030)
W	1.02 (0.040)
A	1.27 (0.050)

PHYSICAL DIMENSIONS AND PAD LAYOUT



PHYSICAL DIMENSIONS

MM (IN.)

	L	W	t
AU16 (0306)	0.81 ± 0.15 (0.032 ± 0.006)	1.60 ± 0.15 (0.063 ± 0.006)	0.13 min. (0.005 min.)
AU17 (0508)	1.27 ± 0.25 (0.050 ± 0.010)	2.00 ± 0.25 (0.080 ± 0.010)	0.13 min. (0.005 min.)
AU18 (0612)	1.60 ± 0.25 (0.063 ± 0.010)	3.20 ± 0.25 (0.126 ± 0.010)	0.13 min. (0.005 min.)

T - See Range Chart for Thickness and Codes

PAD LAYOUT DIMENSIONS

MM (IN.)

	A	B	C
AU16 (0306)	0.31 (0.012)	1.52 (0.060)	0.51 (0.020)
AU17 (0508)	0.51 (0.020)	2.03 (0.080)	0.51 (0.020)
AU18 (0612)	0.76 (0.030)	3.05 (0.120)	0.635 (0.025)

