




CRIMP RINGS & SPADES



✓ Active

TE CONNECTIVITY (TE)
22-16 PIDG NYLON R/T 5/16 RED
[PIDG](#) | [PIDG](#)

150300
TE Internal Number: 150300

[Always EU RoHS/ELV Compliant](#)

- Terminal Shape **Ring Tongue**
- Stud Diameter **8.33 mm [.327 in]**
- Tongue Thickness **.79 mm [.031 in]**
- Sealed **No**
- Heavy Duty **No**

No documentation available.

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	Sealed	No
	Barrel Type	Closed Barrel
	Wire/Cable Type	Stranded
	Insulated	Yes
	Insulated Wire Support	No
	Support Style	Non - Insulation Support
	Stud Size	M8
	Wire/Cable Composition	Stranded

Configuration Features	Terminal Angle	Straight
------------------------	----------------	----------

Electrical Characteristics	Voltage (Max) (V)	300
----------------------------	-------------------	-----

Body Features	Plating Material	Tin
	Plating Thickness	2.54 µm [100 µin]
	Finish	Tin
	Insulation Sleeve Material	Nylon

	Insulation Sleeve Color	Red
	Insulation Material	Nylon
	Body Style	PIDG
Contact Features	Terminal Shape	Ring Tongue
	Terminal Orientation	Straight
Dimensions	Stud Diameter	8.33 mm [.327 in]
	Tongue Thickness	.79 mm [.031 in]
	Wire Size (AWG)	22 – 16
	Wire Size (mm²)	.326 – 1.31
	Wire Size (CMA)	509 – 3260
	Barrel Inside Diameter	3.68 mm [.144 in]
	Material Thickness	.79 mm [.031 in]
	Overall Length	21.74 mm [.856 in]
	Barrel Inside Diameter (Min)	1.65 mm [.065 in]
Usage Conditions	High Temperature Rating	105 °C [221 °F]
	Operating Temperature Range	105 °C [221 °F]
Operation/Application	Heavy Duty	No
Industry Standards	Government Qualified	No
Packaging Features	Packaging Method	Box
	Packaging Quantity	1000
Other	Barrel Color	Red
Product Compliance	Statement of Compliance PDF	
	VIEW ALL PRODUCT COMPLIANCE	