




rev	ecn no	dr	date
A	V06-1178	LP	2006-12-12
B	V07-0440	LP	2007-07-05
C	V08-0198	LP	2008-04-28
D	V09-0071	PK	2009-02-24
-	-	-	-

A

B

C

D





spec ref		-		dr	Bill Lin	2010/02/02	projection		mm		size	A4	scale	1:1
tolerance std	ASME Y14.5	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	Nickor Zuo	2011/05/26	ecn no					ELX-DG-003943-1			
			chr	Alex Cao	2011/06/24									
			appr	Pei-Ming Zheng	2011/06/27	product family		GIG-Array		rel level		Released		
surface		linear	0.X	±0.30		title	GIG-Array		dwg no	10026804		rev	E	
			0.XX	±0.10										
			0.XXX	±0.05										
ASME Y14.5		angular	0°	±2°	www.fci.com	cat. no.	-	Product - Customer Drw		sheet 1 of 5				

Print File - REV C - 2009-06-09



Copyright FCI.




spec ref -				dr Bill Lin 2010/02/02		projection 	mm 	size A4	scale 1:1
tolerance std ASME Y14.5 -	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng Nickor Zuo 2011/05/26				ecn no ELX-DG-003943-1	
				chr Alex Cao 2011/06/24				rel level Released	
				appr Pei-Ming Zheng 2011/06/27					
surface 3.2		linear	0.X	±0.30		title GIG-Array 10mm PLUG ASSY. 296 SIG. POS.		dwg no 10026804	rev E
ASME Y14.5			0.XX	±0.10					
			0.XXX	±0.05					
		angular	0°	±2°	www.fci.com	cat. no. - Product - Customer Drw		sheet 2 of 5	


Print File - REV C - 2009-06-09



Copyright FCI.



PLUG INTERFACE
DESCRIPTION



spec ref -				dr Bill Lin 2010/02/02		projection 	mm 	size A4	scale 1:1	
tolerance std ASME Y14.5 -	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng Nickor Zuo 2011/05/26				ecn no ELX-DG-003943-1		
				chr Alex Cao 2011/06/24				rel level Released		
				appr Pei-Ming Zheng 2011/06/27						
					product family GIG-Array					
surface $\sqrt{3.2}$ ASME Y14.5	linear	0.X	±0.30		title GIG-Array			dwg no 10026804	rev E	
		0.XX	±0.10							
		0.XXX	±0.05		10mm PLUG ASSY. 296 SIG. POS.					
	angular 0° ±2°									
www.fci.com				cat. no. -		Product - Customer Drw		sheet 3 of 5		

PrintE File - REV C - 2009-06-09




Copyright FCI.

FLAT AREA
PICK-UP CAP



END VIEW OF MATED CONNECTORS

DIM. "A"	RECPT. ASSY. P/N
17	55701
22	10032376
27	55733

spec ref -				dr Bill Lin 2010/02/02		projection 	mm 	size A4	scale 1:1
tolerance std ASME Y14.5 -	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng Nickor Zuo 2011/05/26	ecn no ELX-DG-003943-1				
				chr Alex Cao 2011/06/24	rel level Released				
				appr Pei-Ming Zheng 2011/06/27					
surface 3.2 ASME Y14.5	linear	0.X	±0.30		title GIG-Array 10mm PLUG ASSY. 296 SIG. POS.			dwg no 10026804	rev E
		0.XX	±0.10						
		0.XXX	±0.05						
ASME Y14.5		angular	0°	±2°	www.fci.com	cat. no. -	Product - Customer Drw		sheet 4 of 5

PrintE File - REV C - 2009-06-09


PRODUCT NUMBER	SOLDER BALL COMPOSITION	CONTACT PLATING PERFORMANCE LEVEL
10026804-001	STANDARD (EUTECTIC)	PERFORMANCE-BASED PLATING, QUALIFIED TO MEET THE REQUIREMENTS OF FCI PRODUCT SPECIFICATION GS-12-192, INCLUDING TELCORDIA CENTRAL OFFICE
10026804-001LF	LEADFREE	

NOTES:

- ① MAT'L:
HOUSING: LCP
CONTACT: COPPER ALLOY
PLATING (CONTACT): Au OVER Ni.
UL RATING: 94 V-0
- ② SOLDER BALLS WILL NOT BE PERFECT
SPHERICAL SHAPE DUE TO REFLOW ATTACHMENT.
- ③ MATED HEIGHT EFFECTED BY CUSTOMERS'
PCB PAD SIZE, PLATING, SOLDER REFLOW
PROFILE & SOLDER PASTE.
- ④ CONTACTS IN ROWS A,C,E,G,J,K,M,P,R AND T
ARE SINGLE BEAM CONTACTS,
TYPICALLY USED AS GROUND PINS.
(NOTE: CONTACTS IN ROWS J & K ARE
TIED TOGETHER [COMMONED])
- ⑤ CONTACTS IN ROWS B,D,F,H,L,N,Q AND S
ARE DUAL BEAM CONTACTS,
TYPICALLY USED AS SIGNAL PINS.

NOTES CONTINUED

- ⑥ SPECIFIED POSITIONAL TOLERANCE DEFINES PAD TO PAD
LOCATION WITHIN LAND PATTERN. POSITIONAL TOLERANCE
OF LAND PATTERN TO FUDICIAL MARKS OR PCB DATUMS
SHALL BE DEFINED BY CUSTOMER. FOR RECOMMENDED
PRODUCT APPLICATION AND PCB DESIGN DETAILS, SEE
DOC. NO. GS-20-016.
- ⑦ FOR PROPER APPLICATION FOLLOW FCI APPLICATION
SPECIFICATION GS-20-033 LEADFREE SOLDER BALLS
WILL NOT SOLDER PROPERLY IN A LEADED SOLDER
PROCESS DUE TO A HIGHER REFLOW TEMPERATURE,
LEADFREE PRODUCT IS THEREFORE NOT BACKWARDS
COMPATIBLE WITH LEADED OR SOME SOLDERING
APPLICATIONS. REFERENCE FCI APPLICATION
SPECIFICATION.
- ⑧ THIS PRODUCT MEETS THE EUROPEAN UNION
DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED
IN GS-22-008. PRODUCT MEETING WITH THE DIRECTIVE IS
IDENTIFIED IN THE LOT CODE NUMBER MARKED ON EACH
PART BY HAVING AN "X" IN THE SEVENTH CHARACTER POSITION.

spec ref		-		dr	Bill Lin	2010/02/02	projection 	mm 	size	A4	scale	1:1	
tolerance std ASME Y14.5	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Nickor Zuo	2011/05/26			ecn no	ELX-DG-003943-1			
				chr	Alex Cao	2011/06/24			rel level			Released	
				appr	Pei-Ming Zheng	2011/06/27	product family		GIG-Array				
surface 3.2 	linear	0.X	±0.30		title GIG-Array 10mm PLUG ASSY. 296 SIG. POS.				dwg no	10026804		rev E	
		0.XX	±0.10										
		0.XXX	±0.05										
ASME Y14.5	angular	0°	±2°	www.fci.com	cat. no.		-	Product - Customer Drw			sheet 5 of 5		

PrintE File - REV C - 2009-06-09