

Complementary Silicon Power Transistors

D44VH10 (NPN), D45VH10 (PNP)

These complementary silicon power transistors are designed for high-speed switching applications, such as switching regulators and high frequency inverters. The devices are also well-suited for drivers for high power switching circuits.

Features

- Fast Switching
- Key Parameters Specified @ 100 °C
- Low Collector-Emitter Saturation Voltage
- Complementary Pairs Simplify Circuit Designs
- These Devices are Pb-Free and are RoHS Compliant*

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Collector-Emitter Voltage	V_{CEO}	80	Vdc
Collector-Emitter Voltage	V_{CEV}	100	Vdc
Emitter Base Voltage	V_{EB}	7.0	Vdc
Collector Current – Continuous	I_C	15	Adc
Collector Current – Peak (Note 1)	I_{CM}	20	Adc
Total Power Dissipation @ $T_C = 25\text{ °C}$ Derate above 25 °C	P_D	83 0.67	W W/°C
Operating and Storage Junction Temperature Range	T_J, T_{stg}	–55 to 150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.



1. Pulse Width ≤ 6.0 ms, Duty Cycle $\leq 50\%$.

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction to Case	$R_{\theta JC}$	1.5	°C/W
Thermal Resistance, Junction to Ambient	$R_{\theta JA}$	62.5	°C/W
Maximum Lead Temperature for Soldering Purposes: 1/8" from Case for 5 Seconds	T_L	275	°C

*For additional information on our Pb-Free strategy and soldering details, please download the **onsemi** Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

15 A COMPLEMENTARY SILICON POWER TRANSISTORS 80 V, 83 W



TO-220
CASE 221A
STYLE 1

MARKING DIAGRAM



x = 4 or 5
A = Assembly Location
Y = Year
WW = Work Week
G = Pb-Free Package

ORDERING INFORMATION

Device	Package	Shipping
D44VH10G	TO-220 (Pb-Free)	50 Units/Rail
D45VH10G	TO-220 (Pb-Free)	50 Units/Rail

D44VH10 (NPN), D45VH10 (PNP)

ELECTRICAL CHARACTERISTICS (T_C = 25 °C unless otherwise noted)

Characteristic	Symbol	Min	Typ	Max	Unit
OFF CHARACTERISTICS					
Collector-Emitter Sustaining Voltage (Note 2) (I _C = 25 mAdc, I _B = 0)	V _{CEO(sus)}	80	–	–	Vdc
Collector-Emitter Cutoff Current (V _{CE} = Rated V _{CEV} , V _{BE(off)} = 4.0 Vdc) (V _{CE} = Rated V _{CEV} , V _{BE(off)} = 4.0 Vdc, T _C = 100 °C)	I _{CEV}	– –	– –	10 100	μAdc
Emitter Base Cutoff Current (V _{EB} = 7.0 Vdc, I _C = 0)	I _{EBO}	–	–	10	μAdc

ON CHARACTERISTICS (Note 2)

DC Current Gain (I _C = 2.0 Adc, V _{CE} = 1.0 Vdc) (I _C = 4.0 Adc, V _{CE} = 1.0 Vdc)	h _{FE}	35 20	– –	– –	–
Collector-Emitter Saturation Voltage (I _C = 8.0 Adc, I _B = 0.4 Adc) D44VH10 (I _C = 8.0 Adc, I _B = 0.8 Adc) D45VH10 (I _C = 15 Adc, I _B = 3.0 Adc, T _C = 100 °C) D44VH10 D45VH10	V _{CE(sat)}	– – – –	– – – –	0.4 1.0 0.8 1.5	Vdc
Base-Emitter Saturation Voltage (I _C = 8.0 Adc, I _B = 0.4 Adc) D44VH10 (I _C = 8.0 Adc, I _B = 0.8 Adc) D45VH10 (I _C = 8.0 Adc, I _B = 0.4 Adc, T _C = 100 °C) D44VH10 (I _C = 8.0 Adc, I _B = 0.8 Adc, T _C = 100 °C) D45VH10	V _{BE(sat)}	– – – –	– – – –	1.2 1.0 1.1 1.5	Vdc

DYNAMIC CHARACTERISTICS

Current Gain Bandwidth Product (I _C = 0.1 Adc, V _{CE} = 10 Vdc, f = 20 MHz)	f _T	–	50	–	MHz
Output Capacitance (V _{CB} = 10 Vdc, I _C = 0, f _{test} = 1.0 MHz) D44VH10 D45VH10	C _{ob}	– –	120 275	– –	pF

SWITCHING CHARACTERISTICS

Delay Time	(V _{CC} = 20 Vdc, I _C = 8.0 Adc, I _{B1} = I _{B2} = 0.8 Adc)	t _d	–	–	50	ns
Rise Time		t _r	–	–	250	
Storage Time		t _s	–	–	700	
Fall Time		t _f	–	–	90	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

2. Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2%.

D44VH10 (NPN), D45VH10 (PNP)




Figure 1. D44VH10 DC Current Gain




Figure 2. D45VH10 DC Current Gain




Figure 3. D44VH10 DC Current Gain




Figure 4. D45VH10 DC Current Gain




Figure 5. D44VH10 ON-Voltage




Figure 6. D45VH10 ON-Voltage

D44VH10 (NPN), D45VH10 (PNP)




Figure 7. D44VH10 ON-Voltage




Figure 8. D45VH10 ON-Voltage




Figure 9. Maximum Rated Forward Bias Safe Operating Area




Figure 10. Power Derating





Figure 11. Thermal Response




TO-220-3 10.10x15.12x4.45, 2.54P

CASE 221A

ISSUE AL

DATE 05 FEB 2025



MILLIMETERS			
DIM	MIN	NOM	MAX
A	4.07	4.45	4.83
A1	1.15	1.28	1.41
A2	2.04	2.42	2.79
b	1.15	1.34	1.52
b1	0.64	0.80	0.96
c	0.36	0.49	0.61
D	9.66	10.10	10.53
D1	8.43	8.63	8.83
E	14.48	15.12	15.75
E1	12.58	12.78	12.98
E2	1.27 REF		

MILLIMETERS			
DIM	MIN	NOM	MAX
e	2.42	2.54	2.66
e1	4.83	5.08	5.33
H1	5.97	6.22	6.47
L	12.70	13.49	14.27
L1	2.80	3.45	4.10
Q	2.54	2.79	3.04
øP	3.60	3.85	4.09
Z	---	---	3.48

NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2018.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION Z DEFINES A ZONE WHERE ALL BODY AND LEAD IRREGULARITIES ARE ALLOWED.

STYLE 1:
PIN 1. BASE
2. COLLECTOR
3. EMITTER
4. COLLECTOR

STYLE 2:
PIN 1. BASE
2. EMITTER
3. COLLECTOR
4. EMITTER

STYLE 3:
PIN 1. CATHODE
2. ANODE
3. GATE
4. ANODE

STYLE 4:
PIN 1. MAIN TERMINAL 1
2. MAIN TERMINAL 2
3. GATE
4. MAIN TERMINAL 2

STYLE 5:
PIN 1. GATE
2. DRAIN
3. SOURCE
4. DRAIN

STYLE 6:
PIN 1. ANODE
2. CATHODE
3. ANODE
4. CATHODE

STYLE 7:
PIN 1. CATHODE
2. ANODE
3. CATHODE
4. ANODE

STYLE 8:
PIN 1. CATHODE
2. ANODE
3. EXTERNAL TRIP/DELAY
4. ANODE

STYLE 9:
PIN 1. GATE
2. COLLECTOR
3. EMITTER
4. COLLECTOR

STYLE 10:
PIN 1. GATE
2. SOURCE
3. DRAIN
4. SOURCE

STYLE 11:
PIN 1. DRAIN
2. SOURCE
3. GATE
4. SOURCE

STYLE 12:
PIN 1. MAIN TERMINAL 1
2. MAIN TERMINAL 2
3. GATE
4. NOT CONNECTED

DOCUMENT NUMBER:	98ASB42148B	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	TO-220-3 10.10x15.12x4.45, 2.54P	PAGE 1 OF 1

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales

