

Chip Beads

Product Top Page

Search by Part No.

Search by Characteristics

Cross Reference

Catalog

Tech Notes

Technical Support Tools

FAQ

MMZ1608S102CTA00



Applications



Commercial Grade

Feature

Signal

Signal line

Series



MMZ

Status



Production (Not Recommended for New Design)

Recommended Alternate Part No. : [MMZ1608S102ATA00](#)



Images are for reference only and show exemplary products.

PDF file of this page



Contact



Documents

Product Lineup

Sample Kits

Size

Length(L)	1.60mm ±0.15mm
Width(W)	0.80mm ±0.15mm
Thickness(T)	0.80mm ±0.15mm
Recommended Land Pattern (A)	0.60mm Nom.
Recommended Land Pattern (B)	0.80mm Nom.
Recommended Land Pattern (C)	0.80mm Nom.

Electrical Characteristics


Impedance at 100MHz	1kΩ ±25%
Rated Current	400mA
DC Resistance (Max.)	450mΩ

Other


Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125°C
Soldering Method	Reflow Iron Soldering
AEC-Q200	No
Packing	Punched (Paper)Taping [180mm Reel, Tape width 8mm]
Package Quantity	4000pcs
Weight	0.004g

Characteristic Graph (This is reference data, and does not guarantee the products characteristics.)

Impedance-R-X



Impedance



Frequency/Hz

Change settings

Change settings

Products

- » Search by Part No. » Search by Characteristics » Distributor Inventory Check
- » Capacitors

» Inductors (Coils)

» EMC Components

» RF Components and Modules

» Voltage / Current / Temperature Protection Devices

» Sensors and Sensor Systems

» Ceramic Switching / Heating, Piezo Components, Buzzers and Microphones

» Transformers

» Ferrites and Accessories

» Noise Suppressing / Magnetic Sheet
- » Anechoic Chambers and Radio Wave Absorbers

» Power Supplies

» Magnets

» Flash Storages

» Wireless Power Transfer

» FA Systems

» Transparent Conductive Film

» Micro Modules (Substrates with Built-in ICs, Products Utilizing with SESUB)

» Solar Cells

» Biosensor

Application Guides

Technical Support

Tech Library

Environment

Contact

News

Home

- About TDK
- TDK Worldwide

