



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-17-008525	14JUN2017	HZ	RS


D



C



ASSEMBLY CONNECTIVITY	
FULLAXS LC	FULLAXS LC
PIN A	PIN A
PIN B	PIN B



STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-2061726-Y	XY.0
8-2061726-1	0.6 ±0.05

B

NOTES:

- 1 ASSEMBLY CONNECTIVITY A-A & B-B
- 2 MAX. CONNECTOR ATTENUATION 0.3 dB, MEASURED AT 1310 nm AND 1550 nm, ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B
- 2 MIN. RETURN LOSS 45 dB, IN MATED CONDITION AGAINST REFERENCE CONNECTOR AT 1310 nm AND 1550 nm
- 4 INFORMATION ON LABEL, SEE DETAIL FOR EXAMPLE
- BARCODE
 - UNIQUE TE SERIAL NUMBER
 - ASSEMBLY LENGTH
 - TE CONNECTIVITY PART NUMBER & ORDER NUMBER
- 5 CABLE INFORMATION:
- CORE DIAMETER: 9/125 µm
 - OUTER JACKET DIAMETER: 4.8 mm
 - OUTER JACKET COLOUR: BLACK
 - OUTER JACKET MATERIAL: HALOGEN FREE FLAME RETARDANT
 - CABLE ATTENUATION: 0.40 dB/km @ 1310 nm OR 0.25 dB/km @ 1550 nm
- 6 LENGTHS MEASURED TO TIP OF FULLAXS LC FERRULE

A

4 LABEL DETAIL:



1	INFORMATION LABEL	3
2	FULLAXS OVERMOLDED LC DUPLEX PLUG ASSEMBLY, SM, BLACK	2
L	FOCAB Ø4.8 mm, 2FOLD, SINGLE MODE G657.A2, BLACK	1
Qty	Description	Item
THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS: mm		15JAN2013
TOLERANCES UNLESS OTHERWISE SPECIFIED:		06FEB2013
MATERIAL		06FEB2013
FINISH		06FEB2013
WEIGHT		0.000000
CUSTOMER DRAWING		000779
SCALE		NTS
SHEET		1 of 1
REV		B
TE Connectivity		
FIBER OPTIC LEAD 4.8 mm FULLAXS LC/DPX - FULLAXS LC/DPX SINGLE MODE G657.A2		
RESTRICTED TO		