

VLS201610ET-100M



Applications	 Commercial Grade
Feature	 Wire Wound
	 Magnetic Shield
	 Ferrite Core
Series Type	VLS-E
Status	 Production (Not Recommended for New Design)
	Recommended Alternate Part No. : VLS201610CX-100M-1 (Interchangeability is not guaranteed.)
Brand	TDK



Size	
Length(L)	2.00mm ±0.10mm
Width(W)	1.60mm ±0.10mm
Thickness Height	0.95mm Max.
Recommended Land Pattern (A)	0.65mm Nom.
Recommended Land Pattern (B)	0.70mm Nom.
Recommended Land Pattern (C)	1.60mm Nom.

Electrical Characteristics	
Inductance	10μH ±20% at 1MHz
Rated Current (L Change) [Typ.]	450mA (30% Down)
Rated Current (L Change) [Max.]	400mA (30% Down)
Rated Current (Temperature Rise) [Typ.]	420mA (40°C Rise)
Rated Current (Temperature Rise) [Max.]	
DC Resistance [Typ.]	1.15Ω
DC Resistance [Max.]	1.38Ω
Rated Voltage [Max.]	
Self Resonant Frequency [Min.]	
Self Resonant Frequency [Typ.]	
Q [Min.]	
Q [Typ.]	

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-40 to 105°C
Soldering Method	Reflow
AEC-Q200	NO
Packing	Embossed (Plastic)Taping [180mm Reel]

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

VLS201610ET-100M









Package Quantity	2000pcs
Weight	0.012g

VLS201610ET-100M




Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)



VLS201610ET-100M



Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)





Associated Images

