

DATA SHEET

ZENER DIODES

GENERAL VOLTAGE REGULATION

BZT52CXXW SERIES

RoHS compliant & Halogen free


Product specification— May 14, 2026 V.1



Zener Diodes

Features

- Total power dissipation: max.500mW
- Zener voltage: 2.4V~75V
- Package: SOD-123
- Moisture sensitivity level 1
- Terminals: Tin plated leads, solderable per J-STD-002 and JESD22-B102



Application

- Linear voltage regulator
- DC regulator
- Small-signal surge protection

Maximum Ratings (Ta = 25°C)

Parameter	Symbol	Value	Unit
Forward Voltage@I _F =10mA	V _F	0.9	V
Power Dissipation	P _D	500	mW
Maximum Regulator Current	I _{ZM}	P _D /V _Z	mA
Junction Temperature	T _J	-55 to +150	°C
Storage Temperature Range	T _{stg}	-55 to +150	°C

Thermal Characteristics

Parameter	Symbol	Max.	Unit
Thermal Resistance Junction to Ambient	R _{θJA} ⁽¹⁾	250	°C/W
Thermal Resistance Junction to Case	R _{θJC} ⁽¹⁾	200	°C/W

⁽¹⁾ Thermal resistance from junction to ambient and from junction to case mounted on P.C.B. with 8mm*9mm copper pad areas.

Electrical Characteristics at Ta = 25°C

Type	Marking Code	Vzt (V)@Izt			Izt	Zzt@Izt	Izk	Zzk@Izk	I _R @V _R	V _R
		Min.	Typ.	Max.	(mA)	Max(Ω)	(mA)	Max(Ω)	Max(uA)	(V)
BZT52C2V4W	WX.	2.2	2.4	2.6	5	100	1.0	600	50	1.0
BZT52C2V7W	W1.	2.5	2.7	2.9	5	100	1.0	600	20	1.0
BZT52C3V0W	W2.	2.8	3.0	3.2	5	95	1.0	600	10	1.0
BZT52C3V3W	W3.	3.1	3.3	3.5	5	95	1.0	600	5	1.0
BZT52C3V6W	W4.	3.4	3.6	3.8	5	90	1.0	600	5	1.0

Type	Marking Code	Vzt (V)@Izt			Izt	Zzt@Izt	Izk	Zzk@Izk	IR@VR	VR
		Min.	Typ.	Max.	(mA)	Max(Ω)	(mA)	Max(Ω)	Max(uA)	(V)
BZT52C3V9W	W5.	3.7	3.9	4.1	5	90	1.0	600	3	1.0
BZT52C4V3W	W6.	4.0	4.3	4.6	5	90	1.0	600	3	1.0
BZT52C4V7W	W7.	4.4	4.7	5.0	5	80	1.0	500	3	2.0
BZT52C5V1W	W8.	4.8	5.1	5.4	5	60	1.0	480	2	2.0
BZT52C5V6W	W9.	5.2	5.6	6.0	5	40	1.0	400	1	2.0
BZT52C6V2W	WA.	5.8	6.2	6.6	5	10	1.0	150	3	4.0
BZT52C6V8W	WB.	6.4	6.8	7.2	5	15	1.0	80	2	4.0
BZT52C7V5W	WC.	7.0	7.5	7.9	5	15	1.0	80	1	5.0
BZT52C8V2W	WD.	7.7	8.2	8.7	5	15	1.0	80	0.7	5.0
BZT52C9V1W	WE.	8.5	9.1	9.6	5	15	1.0	100	0.5	6.0
BZT52C10W	WF.	9.4	10	10.6	5	20	1.0	150	0.2	7.0
BZT52C11W	WG.	10.4	11	11.6	5	20	1.0	150	0.1	8.0
BZT52C12W	WH.	11.4	12	12.7	5	25	1.0	150	0.1	8.0
BZT52C13W	WI.	12.4	13	14.1	5	30	1.0	170	0.1	8.0
BZT52C15W	WJ.	13.8	15	15.6	5	30	1.0	200	0.1	10.5
BZT52C16W	WK.	15.3	16	17.1	5	40	1.0	200	0.1	11.2
BZT52C18W	WL.	16.8	18	19.1	5	45	1.0	225	0.1	12.6
BZT52C20W	WM.	18.8	20	21.2	5	55	1.0	225	0.1	14.0
BZT52C22W	WN.	20.8	22	23.3	5	55	1.0	250	0.1	15.4
BZT52C24W	WO.	22.8	24	25.6	5	70	1.0	250	0.1	16.8
BZT52C27W	WP.	25.1	27	28.9	2	80	0.5	300	0.1	18.9
BZT52C30W	WQ.	28	30	32	2	80	0.5	300	0.1	21.0
BZT52C33W	WR.	31	33	35	2	80	0.5	325	0.1	23.1
BZT52C36W	WS.	34	36	38	2	90	0.5	350	0.1	25.2
BZT52C39W	WT.	37	39	41	2	130	0.5	350	0.1	27.3
BZT52C43W	WU.	40	43	46	5	100	1.0	750	0.1	32
BZT52C47W	WV.	44	47	50	5	100	1.0	750	0.1	35
BZT52C51W	WW.	48	51	54	2	180	0.5	400	0.05	35.7
BZT52C56W	X1.	53	56	59	2	200	1	1000	0.1	42
BZT52C62W	5X2.	58	62	66	2	215	0.5	450	0.05	43.4
BZT52C68W	5X3.	64	68	72	2	240	0.5	475	0.05	47.6
BZT52C75W	5X4.	70	75	79	2	255	0.5	500	0.05	52.5



Electrical Characteristic Curves

Figure 1. Zener Characteristics Curve




Figure 2. Zener Characteristics Curve




Figure 3. Zener Characteristics Curve





Figure 4. P_D - T_a Curve



Dimensions (SOD-123)

Symbol	Dimension (mm)			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	3.55	3.85	0.140	0.152
B	2.55	2.85	0.100	0.112
C	1.40	1.80	0.055	0.071
D	0.95	1.35	0.037	0.053
E	0.51	0.71	0.020	0.028
G	0.15	0.45	0.006	0.018
H	0.08	0.25	0.003	0.010
J	0.00	0.15	0.000	0.006
θ	0	8°	0	8°

Packing

Tape	Symbol	Dimension(mm)
	W	8.00±0.20
	P0	4.00±0.10
	P1	4.00±0.10
	P2	2.00±0.10
	R	Φ1.50±0.10
	R0	Φ1.00±0.25
	E	1.75±0.10
	F	3.50±0.05
	A0	1.75±0.10
	B0	3.94±0.10
	B1	2.59±0.20
	T	0.20±0.02
	T1	1.52±0.10
Reel	D	Φ178±1.0
	D2	Φ13.5±0.30
	W1	9.3±1.5
	Quantity: 3000PCS	

LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non-infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.