








PC board drilling dimensions(after plating)  
(thickness ≤ 3.20±0.30mm)



TIN LEAD PART NUMBER

| SHELL | A±0.38 | B±0.12 | C±0.10 | D±0.25 | E±0.07 | PART NUMBER | PART NUMBER  |
|-------|--------|--------|--------|--------|--------|-------------|--------------|
| 09    | 30.81  | 24.99  | 16.96  | 16.21  | 10.96  | --          | D09S91C6PI9C |
| 15    | 39.14  | 33.32  | 25.18  | 24.54  | 19.18  | --          | D15S91C6PI9C |
| 25    | 53.03  | 47.04  | 39.12  | 38.25  | 33.12  | --          | D25S91C6PI9C |
| 37    | 69.32  | 63.50  | 55.68  | 54.71  | 49.68  | --          | D37S91C6PI9C |
|       |        |        |        |        |        | ---         | 0.76µ gold   |

LEAD FREE PART NUMBER

| SHELL | A±0.38 | B±0.12 | C±0.10 | D±0.25 | E±0.07 | PART NUMBER | PART NUMBER    |
|-------|--------|--------|--------|--------|--------|-------------|----------------|
| 09    | 30.81  | 24.99  | 16.96  | 16.21  | 10.96  | --          | D09S91C6PI9CLF |
| 15    | 39.14  | 33.32  | 25.18  | 24.54  | 19.18  | --          | D15S91C6PI9CLF |
| 25    | 53.03  | 47.04  | 39.12  | 38.25  | 33.12  | --          | D25S91C6PI9CLF |
| 37    | 69.32  | 63.50  | 55.68  | 54.71  | 49.68  | --          | D37S91C6PI9CLF |
|       |        |        |        |        |        | ---         | 0.76µ gold     |

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:  
SEE DRAWING C01-8646-0001

| rev | ecn no    | dr  | date       |
|-----|-----------|-----|------------|
| B   | -         | ATC | 1999/03/05 |
| C   | LS05-004  | MPE | 2005/02/11 |
| D   | LS06-0089 | LGO | 2006/06/15 |
| E   | LS06-0140 | LGO | 2006/09/16 |
| -   | -         | -   | -          |
| -   | -         | -   | -          |
| -   | -         | -   | -          |

|                                                                                       |         |            |                                                        |        |                                   |       |                                                                                                     |              |                                                                                             |  |           |              |
|---------------------------------------------------------------------------------------|---------|------------|--------------------------------------------------------|--------|-----------------------------------|-------|-----------------------------------------------------------------------------------------------------|--------------|---------------------------------------------------------------------------------------------|--|-----------|--------------|
| www.fciconnect.com                                                                    |         |            | surface<br>ISO 1302                                    |        | tolerance std<br>ISO 406 ISO 1101 |       | projection<br> |              | mm<br> |  |           |              |
|                                                                                       |         |            | TOLERANCES UNLESS OTHERWISE SPECIFIED                  |        |                                   |       |                                                                                                     |              |                                                                                             |  |           |              |
| Dr                                                                                    | JOUBERT | 1998/04/24 | ANGULAR                                                | LINEAR | 0.X                               | ±0.1  | size<br>A3                                                                                          | Scale<br>2:1 |                                                                                             |  |           |              |
| Eng                                                                                   | PESSON  | 1998/04/24 |                                                        |        | 0.XX                              | ±0.1  |                                                                                                     |              |                                                                                             |  |           |              |
| Chr                                                                                   | LEGARE  | 1998/04/24 |                                                        |        | 0.XX' ±2°                         | 0.XXX |                                                                                                     |              |                                                                                             |  | ±0.1      |              |
| Appr                                                                                  | LEGARE  | 1998/04/24 | Product family                                         |        |                                   |       | D-SUB                                                                                               | Spec ref -   |                                                                                             |  |           |              |
|  |         |            | title<br>FEMALE CONNECTOR DELTA D<br>STD EUROPE STR PF |        |                                   |       | dwg no<br>C01-8646-0617                                                                             |              |                                                                                             |  | Rev.<br>E |              |
|                                                                                       |         |            | catalog no                                             |        |                                   |       | -                                                                                                   | CUSTOMER     |                                                                                             |  |           | sheet 1 of 1 |