

Johanson Part Number VPDD102W222K1GV001E

Johanson Part Number: VPDD102W222K1GV001E

Johanson Company: JDI

Legacy P/N: 102R18W222KV4E

Size for Capacitors (EIA): 1206

Description: Capacitors HVS PME, 1206, X7R, 1000V, 2200pF±10%, Ni/Sn (RoHS), 7" Reel Embossed Tape

Specification Number: None

Life Cycle Stage: Active

NCNR: No

AEC Q200 Qualified: No

Thickness (Max): 0.067

Schedule B: 8532.24.00.20

Thickness (Min): None

ITAR: No

End Band(Min): 0.01

ECCN: EAR99

End Band (max): 0.030

RoHS Compliance: Yes, RoHS 10/10

Standard Item: Yes

REACH: Yes

Lead Time Typical (Weeks)*: 10

Country of Origin: TW

Length (Min): 0.115

Product Family: Capacitors

Length (Max): 0.135

Product Subfamily: Capacitors High Voltage PME
SMD ≥ 500V

Width (Min):0.052

Capacitance Value: 2200.000

Width (Max): 0.072

Cap Unit of Meas: pF

Part Weight (mg): None

Tolerance: ±10%

Packaged Width (lb) Arm: None

Voltage: 1000.0

Packaging: 7" Reel Embossed Tape

Dielectric Temp Coefficient: X7R

Packaging Qty: 3000

Termination: 68

Operating Temp Range: -55°C to +125°C

Marking: No Mark

Storage Temp Range (Packaged): -65°C to +125°C

Product Release Date: Jan. 2, 2006, 8 a.m.

Storage Temp Range (None Operating): +5°C to +40°C with RH 20% to 70%

Harmonization: 8532.24.00.20

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: <https://www.johansondielectrics.com/high-voltage-mlc-capacitors>

Printed from: www.johansontechnology.com/search/pn-detail/VPDD102W222K1GV001E/