

Part Number : 1301530026
Product Description : Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Automatic Reset, Molded NEMA 5-15 Plug and Tri-Tap Connector, 15A, 120V, 7.62m (25.0') Cord Length
Series Number : 130153
Status : Not Recommended For New Design
Product Category : Power Distribution
Engineering Part Number : 15050-25TTA

Documents and Resources

Drawings

1301530026_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Relevant
EU RoHS	Not Relevant

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	Power Distribution
Series	130153
Description	Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Automatic Reset, Molded NEMA 5-15 Plug and Tri-Tap Connector, 15A, 120V, 7.62m (25.0') Cord Length
Enclosure Rating	NEMA 3R
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	GFCI Industrial Duty, Single Phase
UPC	78678888262

Agency

UL	E66308

Electrical

Current - Maximum per Contact	15.0A
GFCI	Yes-In-line
GFCI Reset	Automatic
Ground Continuity Monitor	No
Open Neutral Relay	Yes
Voltage - Maximum	120V

Physical

Cord Diameter	10.92mm (.430")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	7.62m (25.0')
Cord Type	12/3 SJTW

Downloaded from Arrow.com.

Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Mounting Style	Portable
Number of Receptacles	3
Packaging Type	Bag
Receptacle Type	N/A

Downloaded from Arrow.com.