

COAXIAL ADAPTER, N-precision - SMA, 50 Ohm, jack / jack (female / female)
31_N-SMA-50-51/1--_N

Properties

- Precision interfaces
- Excellent electrical performance
- Premium base materials and platings





Product configuration		
Interface type	Gender	Standard
N-precision	jack (female)	IEC 60169-16_MIL-STD-348A/402_CECC 22210
SMA-precision	jack (female)	IEC 60169-15_MIL-STD-348A/405_CECC 22110

Interface and material data		
N-precision		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Stainless steel	Passivated (Plating)
Body	Stainless steel	Passivated (Plating)
Insulator	PFA / PTFE	
SMA-precision		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	

Electrical data	
Impedance	50 Ω
Interface frequency	18 GHz
VSWR	DC - 18 GHz (≤ 1.025 + 0.007 f GHz)

Mechanical data	
Weight	0.0331 kg
Mating cycles	500

COAXIAL ADAPTER, N-precision - SMA, 50 Ohm, jack / jack (female / female)
31_N-SMA-50-51/1--_N

Environmental data			
Operation temperature		-55 °C ... 70 °C	
Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22660178	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
22660178	31_N-SMA-50-51/1--_NE		Single
Additional Information			
Remarks		Operating specification acc. IEEE Std 287: temperature 13 °C to 33 °C	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2389 / Date of publication: 12.07.2025 / uncontrolled copy