






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	DI	REVISED (ECR-23-171026)	31MAR2023	CI	KT
  ISOMETRIC VIEW					



<TABLE 1>			
TYPE	FINISH	P/N	WIRE RANGE (mm ²)
.025	PRE-TIN	2005098-1	0.22
	GOLD	2005154-1	0.37~0.56
.090	PRE-TIN	1897752-1	0.22~0.56
		368088-1	0.3~0.5
		368087-1	0.85~1.25
	GOLD	368086-1	2.0~2.5
		1-368088-1	0.3~0.5


- NOTE
1. GENERAL TOLERANCE: $\pm 0.3, \pm 3^\circ$
 2. CONDITION OF DELEVRY DBL IN 1st LOCKING POSITION
 3. APPLICABLE PLUG ASS'Y P/N: x-2005431-x
 4. APPLICABLE TAB CONTACT P/N: <TABLE 1>

2	WHITE	PBT	CAP DBL HSG	I	I	I
I	RED	PBT	CAP HSG	I		
	BROWN	PBT	CAP HSG		I	
	WHITE	PBT	CAP HSG			I
NO	FINISH/COLOR	MATERIAL	DESCRIPTION	Q'TY		

HYB 34P CAP ASS'Y	HYB 34P CAP ASS'Y	HYB 34P CAP ASS'Y	DESCRIPTION
2005434-6	2005434-4	2005434-1	ASS'Y P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH ±

DWN
CH PARK

CHK
JW JUNG

APVD
HG CHO

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME
025/090 HYBRID 34P CAP ASS'Y

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-2005434

RESTRICTED TO

SCALE
1:1

SHEET
1

OF
1

REV
DI

TE Connectivity